

**General Information**

<b>Extended Product Type:</b>	MCBH-01
<b>Product ID:</b>	1SFA611605R1110
<b>EAN:</b>	7320500307502
<b>Catalog Description:</b>	MCBH-01 CONTACT BLOCK
<b>Long Description:</b>	Modular contact block with holder

**Categories**

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

**Ordering**

<b>EAN:</b>	7320500307502
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369001

**Dimensions**

<b>Product Net Width:</b>	0.048 m
<b>Product Net Height:</b>	0.030 m
<b>Product Net Depth:</b>	0.036 m
<b>Product Net Weight:</b>	0.021 kg

**Container Information**

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	0.11 m
<b>Package Level 1 Height:</b>	0.03 m
<b>Package Level 1 Length:</b>	0.15 m
<b>Package Level 1 Gross Weight:</b>	0.021 kg

**Environmental**

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

**Additional Information**

<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
<b>Device:</b>	Holder for blocks incl.
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Illumination:</b>	Non-illuminated
<b>Mechanical Durability ( ):</b>	10 million
<b>Number of Auxiliary Contacts NC:</b>	1
<b>Product Main Type:</b>	MCBH
<b>Product Name:</b>	CONTACT BLOCK
<b>Product Range:</b>	Modular
<b>Rated Frequency (f<sub>r</sub>):</b>	Supply Circuit 50 Hz Supply Circuit 60 Hz
<b>Rated Operational Current AC-15 (I<sub>e</sub>):</b>	(220 / 240V) 6 A (24 / 127V) 8 A
<b>Rated Operational Current DC-13 (I<sub>e</sub>):</b>	(125V) 1.1 A (24V) 5 A
<b>RoHS Date:</b>	0635 4

**Certificates and Declarations (Document Number)**

<b>Declaration of Conformity - CE:</b>	1SFA1-83;
--	-----------

**Classifications**

<b>E-nummer:</b>	3714020
<b>ETIM 4.0:</b>	EC002611 - Control switch
<b>ETIM 5.0:</b>	EC002611 - Control switch
<b>Object Classification Code:</b>	S
<b>UNSPSC:</b>	39121500