


FEATURES:

- CW light source with integrated wavelength locker
- Output Power: 13dBm (min.)
- Tunable over 8 ITU-T 50GHz spaced channels (2.8nm)
- Available at C-band ITU-T grid wavelengths between 1528.773 to 1570.005nm
- Wavelength stability better than $\pm 25\text{pm}$ drift over 20 years operation and (0 to 70°C) case temperature variation
- Built-in optical isolator, Thermistor, TEC, Wavelength Monitor PIN-PD, Power Monitor PIN-PD
- Polarization maintaining (PANDA) fiber



APPLICATIONS:

Long haul DWDM transmission system
Metropolitan DWDM transmission system
Optical Test Equipment

DESCRIPTION:

The Eudyna Tunable LD module with Wavelength Locker (FLD5F15CA-R) is a high power CW laser (13dBm) with polarization maintaining fiber. It is intended for use with an external modulator. The oscillation wavelength can be tuned across a 2.8nm range (8 ITU-T 50GHz spaced channels) via adjustment of the chip temperature with the built-in TEC. The tuned wavelength can be locked onto the desired ITU-T grid channel via use of the built-in Wavelength Monitor. This laser is available at any of the 104 ITU-T wavelengths in the C-band (1528.773 to 1570.005nm). The device comes in a standard 14-pin butterfly package, and operates between 0 to 70°C.

ABSOLUTE MAXIMUM RATINGS ($T_c=25^\circ\text{C}$, unless otherwise specified)

Parameter	Symbol	Condition	Ratings		Unit
			Min.	Max.	
Storage Temperature	T_{stg}	-	-40	+85	$^\circ\text{C}$
Operating Case Temperature	T_{op}	-	0	+70	$^\circ\text{C}$
Optical Output Power	P_f	CW	-	30	mW
LD Forward Current	I_f	CW	-	300	mA
LD Reverse Voltage	V_R	-	-	2	V
PD Reverse Voltage	V_{DR}	-	-	20	V
PD Forward Current	I_{PF}	-	-	10	mA
Cooler Voltage	V_c	Cooling	-	+5.00	V
		Heating	-2.50	-	
Cooler Current	I_c	Cooling	-	+1.85	A
		Heating	-0.60	-	
Thermistor Temperature	T_{th}	ATC Operation	0	+70	$^\circ\text{C}$
Lead Soldering Time	-	260°C	-	10	sec

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_L=T_{set}$, (CH.1 to CH.8) $T_C=25^\circ\text{C}$, BOL, unless otherwise specified)

Parameter	Symbol	Test Conditions	Limits			Unit
			Min.	Typ.	Max.	
Laser Set Temperature (BOL)	T_{set}	-	11	-	47	$^\circ\text{C}$
Laser Set Temperature (EOL)	T_{set}	-	10	-	48	$^\circ\text{C}$
Optical Output Power	P_f	-	20	-	-	mW
Threshold Current	I_{th}	-	3	-	45	mA
Forward Voltage	V_F	-	-	-	2.2	V
Slope Efficiency	η	-	-	0.14	-	mW/mA
Operating Forward Current	I_{op}	-	-	-	250	mA
Peak Wavelength	λ_p	CH.1 to CH.8, ORL>40dB	Note (4)			nm
Wavelength Stability with Case Temperature and Aging	-	$I_{m1}, I_{m2}=\text{constant}$, $T_c=0$ to 70°C , 20 years	-25	-	+25	pm
Wavelength Stability with LD Current Change	-	$T_L=T_{set}$	-	-	25	pm/mA
Spectral Width (-3dB)	$\Delta\lambda$	ORL>40dB	-	3	10	MHz
Side Mode Suppression	S_r		33	-	-	dB
Power Monitor Current	I_{m1}	$P_f=20\text{mW}$	0.1	-	1.8	mA
Power Monitor Dark Current	I_{dm1}	$V_{pd}=5\text{V}$	-	-	100	nA
Power Monitor Capacitance	C_{t1}	$V_{pd}=5\text{V}$, $f=1\text{MHz}$	-	-	10	pF
Wavelength Monitor Current	I_{m2}	$P_f=20\text{mW}$, WL Locked	0.1	-	1.8	mA
Wavelength Monitor Dark Current	I_{dm2}	$V_{pd}=5\text{V}$	-	-	100	nA
Wavelength Monitor Capacitance	C_{t2}	$V_{pd}=5\text{V}$, $f=1\text{MHz}$	-	-	10	pF
Wavelength difference between lock point and $I_{m2\text{peak}}$ (Note 2)	$\Delta\lambda$ locked		17.0	-	33.0	GHz
I_{m2} peak/bottom Ratio	$I_{m2\text{peak}}/I_{m2\text{bottom}}$		1.0	-	4.5	dB
Tracking Error (Note 3)	TE	$I_{m1,2}=\text{constant}$, $T_c=0$ to $+70^\circ\text{C}$	-0.5	-	+0.5	dB
Optical Isolation	I_S	$T_c=0$ to $+70^\circ\text{C}$	22	-	-	dB
Polarization Extinction Ratio	PER		20	-	-	dB
Relative Intensity Noise	RIN	CW, ORL>40dB average of $f=\text{DC}$ to 7.5GHz	-	-	-140	dB/Hz
Cooler Current	I_c	$T_L=T_{set}$, $T_c=+70^\circ\text{C}$	-	-	1.05	A
Cooler Voltage	V_c		-	-	3.80	V
Cooler Power	P_c		-	-	4.00	W
Thermistor Resistance	R_{th}	$T_L=25^\circ\text{C}$, $T_c=+25^\circ\text{C}$	9.5	10.0	10.5	k Ω
Thermistor B Constant (Note 2)	B		3,270	3,450	3,630	K

Note 1. $TE=10\cdot\log[P_f(T_c)/P_f(25)]$

Note 2. Relation between resistance and temperature ($^\circ\text{K}$) is: $R_{th}(T) = R_{th}(25^\circ\text{C})\cdot\exp[B(1/T-1/298)]$

Note 3. At the shortest wavelength of each sub-band, wavelength at lock point is longer than I_{m2} peak. (Increasing wavelength shall give a decrease in wavelength monitor current) The value is written in frequency: $f=c/\lambda_p$, $c=2.99792458\cdot 10^8\text{m/s}$

Note 4. Reference Table 1 for Wavelength Table

Fig. 1 Forward Current vs Output Power




Fig. 2 Temperature Dependence of Wavelength(ACC Operation)




Fig. 3 Cooler Voltage -Current




Fig.4 Spectrum




Fig. 5 Filter Curve




Table 1 Wavelength Table

Part Number	Wavelength (nm) (TL=Tset) (in vacuum)	Tolerance (nm)	Locking Curve Slope	Part Number	Wavelength (nm) (TL=Tset) (in vacuum)	Tolerance (nm)	Locking Curve Slope
FLD5F15CA-R9610	1528.773	±0.01	Negative	FLD5F15CA-R9290	1554.134	±0.01	Negative
	1529.163	±0.01	Positive		1554.537	±0.01	Positive
	1529.553	±0.01	Negative		1554.940	±0.01	Negative
	1529.944	±0.01	Positive		1555.343	±0.01	Positive
	1530.334	±0.01	Negative		1555.747	±0.01	Negative
	1530.725	±0.01	Positive		1556.151	±0.01	Positive
	1531.116	±0.01	Negative		1556.555	±0.01	Negative
FLD5F15CA-R9570	1531.507	±0.01	Positive		1556.959	±0.01	Positive
	1531.898	±0.01	Negative	FLD5F15CA-R9250	1557.363	±0.01	Negative
	1532.290	±0.01	Positive		1557.768	±0.01	Positive
	1532.681	±0.01	Negative		1558.173	±0.01	Negative
	1533.073	±0.01	Positive		1558.578	±0.01	Positive
	1533.465	±0.01	Negative		1558.983	±0.01	Negative
	1533.858	±0.01	Positive		1559.389	±0.01	Positive
FLD5F15CA-R9530	1534.250	±0.01	Negative		1559.794	±0.01	Negative
	1534.643	±0.01	Positive		1560.200	±0.01	Positive
	1535.036	±0.01	Negative	FLD5F15CA-R9210	1560.606	±0.01	Negative
	1535.429	±0.01	Positive		1561.013	±0.01	Positive
	1535.822	±0.01	Negative		1561.419	±0.01	Negative
	1536.216	±0.01	Positive		1561.826	±0.01	Positive
	1536.609	±0.01	Negative		1562.233	±0.01	Negative
	1537.003	±0.01	Positive		1562.640	±0.01	Positive
	1537.397	±0.01	Negative		1563.047	±0.01	Negative
FLD5F15CA-R9490	1537.792	±0.01	Positive		1563.455	±0.01	Positive
	1538.186	±0.01	Negative	FLD5F15CA-R9170	1563.863	±0.01	Negative
	1538.581	±0.01	Positive		1564.271	±0.01	Positive
	1538.976	±0.01	Negative		1564.679	±0.01	Negative
	1539.371	±0.01	Positive		1565.087	±0.01	Positive
	1539.766	±0.01	Negative		1565.496	±0.01	Negative
	1540.162	±0.01	Positive		1565.905	±0.01	Positive
FLD5F15CA-R9450	1540.557	±0.01	Negative		1566.314	±0.01	Negative
	1540.953	±0.01	Positive		1566.723	±0.01	Positive
	1541.349	±0.01	Negative	FLD5F15CA-R9130	1567.133	±0.01	Negative
	1541.746	±0.01	Positive		1567.542	±0.01	Positive
	1542.142	±0.01	Negative		1567.952	±0.01	Negative
	1542.539	±0.01	Positive		1568.362	±0.01	Positive
	1542.936	±0.01	Negative		1568.773	±0.01	Negative
	1543.333	±0.01	Positive		1569.183	±0.01	Positive
	1543.730	±0.01	Negative		1569.594	±0.01	Negative
FLD5F15CA-R9410	1544.128	±0.01	Positive		1570.005	±0.01	Positive
	1544.526	±0.01	Negative				
	1544.924	±0.01	Positive				
	1545.322	±0.01	Negative				
	1545.720	±0.01	Positive				
	1546.119	±0.01	Negative				
	1546.518	±0.01	Positive				
FLD5F15CA-R9370	1546.917	±0.01	Negative				
	1547.316	±0.01	Positive				
	1547.715	±0.01	Negative				
	1548.115	±0.01	Positive				
	1548.515	±0.01	Negative				
	1548.915	±0.01	Positive				
	1549.315	±0.01	Negative				
FLD5F15CA-R9330	1549.715	±0.01	Positive				
	1550.116	±0.01	Negative				
	1550.517	±0.01	Positive				
	1550.918	±0.01	Negative				
	1551.319	±0.01	Positive				
	1551.721	±0.01	Negative				
	1552.122	±0.01	Positive				
FLD5F15CA-R9330	1552.524	±0.01	Negative				
	1552.926	±0.01	Positive				
	1553.329	±0.01	Negative				
	1553.731	±0.01	Positive				


NOTE

Negative slope: Increasing wavelength shall give a decrease in wavelength monitor current.


Positive slope: Increasing wavelength shall give an increase in wavelength monitor current.

"CA" PACKAGE

UNIT: mm



TOP VIEW



#	PIN DESIGNATIONS
1	Thermistor
2	Thermistor
3	LD Cathode
4	Power Monitor Anode
5	Power Monitor Cathode
6	Thermoelectric Cooler (+)
7	Thermoelectric Cooler (-)
8	Wavelength Monitor Cathode
9	Wavelength Monitor Anode
10	NC
11	LD Anode
12	LD Cathode
13	LD Anode
14	NC

* Pigtail length (L) and connector type are specified in the detail (individual) specification.
L = 1500MIN. for standard

For further information please contact:

Eudyna Devices USA Inc.

2355 Zanker Rd.
San Jose, CA 95131-1138, U.S.A.
TEL: (408) 232-9500
FAX: (408) 428-9111
www.us.eudyna.com

Eudyna Devices Europe Ltd.

Network House
Norreys Drive
Maidenhead, Berkshire SL6 4FJ
United Kingdom
TEL: +44 (0) 1628 504800
FAX: +44 (0) 1628 504888

Eudyna Devices Asia Pte Ltd.

Hong Kong Branch
Rm. 1101, Ocean Centre, 5 Canton Rd.
Tsim Sha Tsui, Kowloon, Hong Kong
TEL: +852-2377-0227
FAX: +852-2377-3921

Eudyna Devices Inc.

Sales Division
1, Kanai-cho, Sakae-ku
Yokohama, 244-0845, Japan
TEL: +81-45-853-8156
FAX: +81-45-853-8170

CAUTION

Eudyna Devices Inc. products contain **gallium arsenide (GaAs)** which can be hazardous to the human body and the environment. For safety, observe the following procedures:

- Do not put this product into the mouth.
- Do not alter the form of this product into a gas, powder, or liquid through burning, crushing, or chemical processing as these by-products are dangerous to the human body if inhaled, ingested, or swallowed.
- Observe government laws and company regulations when discarding this product. This product must be discarded in accordance with methods specified by applicable hazardous waste procedures.

Eudyna Devices Inc. reserves the right to change products and specifications without notice. The information does not convey any license under rights of Eudyna Devices Inc. or others.

© 2004 Eudyna Devices USA Inc.
Printed in U.S.A.