


## High voltage power Schottky rectifier

Datasheet - production data



### Features

- High junction temperature capability
- Good trade off between leakage current and forward voltage drop
- Low leakage current
- Avalanche capability specified
- Insulated package: TO-220FPAB
  - Insulating voltage = 2000 V<sub>RMS</sub> sine
- ECOPACK®2 compliant component for D2PAK on demand

### Description

Dual center tap Schottky rectifier designed for high frequency switch mode power supply.

Table 1: Device summary

| Symbol      | Value    |
|-------------|----------|
| $I_{F(AV)}$ | 2 x 15 A |
| $V_{RRM}$   | 150 V    |
| $T_j$ (max) | 175 °C   |
| $V_F$ (typ) | 0.69 V   |

# 1 Characteristics

**Table 2: Absolute ratings (limiting values, per diode, at 25 °C, unless otherwise specified)**

| Symbol<br>I         | Parameter                                             |                                      |                         |            | Value       | Unit |
|---------------------|-------------------------------------------------------|--------------------------------------|-------------------------|------------|-------------|------|
| V <sub>RRM</sub>    | Repetitive peak reverse voltage                       |                                      |                         |            | 150         | V    |
| I <sub>F(RMS)</sub> | Forward rms current                                   |                                      |                         |            | 30          | A    |
| I <sub>F(AV)</sub>  | Average forward current δ = 0.5, square wave          | TO-220FPAB                           | T <sub>C</sub> = 120 °C | Per diode  | 15          | A    |
|                     |                                                       |                                      | T <sub>C</sub> = 90 °C  | Per device | 30          |      |
|                     |                                                       | TO-220AB, D <sup>2</sup> PAK, TO-247 | T <sub>C</sub> = 155 °C | Per diode  | 15          |      |
|                     |                                                       |                                      | T <sub>C</sub> = 150 °C | Per device | 30          |      |
| I <sub>FSM</sub>    | Surge non repetitive forward current                  | tp = 10 ms sinusoidal                |                         |            | 220         | A    |
| P <sub>ARM</sub>    | Repetitive peak avalanche power                       | tp = 10 μs, Tj = 125 °C              |                         |            | 750         | W    |
| T <sub>stg</sub>    | Storage temperature range                             |                                      |                         |            | -65 to +175 | °C   |
| Tj                  | Maximum operating junction temperature <sup>(1)</sup> |                                      |                         |            | +175        | °C   |

**Notes:**

<sup>(1)</sup>(dP<sub>tot</sub>/dT<sub>j</sub>) < (1/R<sub>th(j-a)</sub>) condition to avoid thermal runaway for a diode on its own heatsink.

**Table 3: Thermal parameter**

| Symbol               | Parameter        |                                      |           | Max. value | Unit |
|----------------------|------------------|--------------------------------------|-----------|------------|------|
| R <sub>th(j-c)</sub> | Junction to case | TO-220AB, D <sup>2</sup> PAK         | Per diode | 1.6        | °C/W |
|                      |                  | TO-220FPAB                           |           | 4          |      |
|                      |                  | TO-247                               |           | 1.5        |      |
|                      |                  | TO-220AB, D <sup>2</sup> PAK         | Total     | 0.85       |      |
|                      |                  | TO-220FPAB                           |           | 3.3        |      |
|                      |                  | TO-247                               |           | 0.8        |      |
| R <sub>th(c)</sub>   | Coupling         | TO-220AB, D <sup>2</sup> PAK, TO-247 | -         | 0.1        | °C/W |
|                      |                  | TO-220FPAB                           |           | 2.6        |      |

When the diodes 1 and 2 are used simultaneously:

$$\Delta T_j (\text{diode1}) = P_{(\text{diode1})} \times R_{th(j-c)} (\text{per diode}) + P_{(\text{diode2})} \times R_{th(c)}$$

Table 4: Static electrical characteristics (per diode)

| Symbol      | Parameter               | Test conditions                     |                     | Min. | Typ. | Max. | Unit          |
|-------------|-------------------------|-------------------------------------|---------------------|------|------|------|---------------|
| $I_R^{(1)}$ | Reverse leakage current | $T_J = 25\text{ }^{\circ}\text{C}$  | $V_R = V_{RRM}$     | -    |      | 6.5  | $\mu\text{A}$ |
|             |                         | $T_J = 125\text{ }^{\circ}\text{C}$ |                     | -    |      | 8.0  | mA            |
| $V_F^{(2)}$ | Forward voltage drop    | $T_J = 25\text{ }^{\circ}\text{C}$  | $I_F = 15\text{ A}$ | -    |      | 0.92 | V             |
|             |                         | $T_J = 125\text{ }^{\circ}\text{C}$ |                     | -    | 0.69 | 0.75 |               |
|             |                         | $T_J = 25\text{ }^{\circ}\text{C}$  | $I_F = 30\text{ A}$ | -    |      | 1    |               |
|             |                         | $T_J = 125\text{ }^{\circ}\text{C}$ |                     | -    | 0.8  | 0.86 |               |

**Notes:**

<sup>(1)</sup>Pulse test:  $t_p = 5\text{ ms}$ ,  $\delta < 2\%$


<sup>(2)</sup>Pulse test:  $t_p = 380\text{ }\mu\text{s}$ ,  $\delta < 2\%$

To evaluate the conduction losses use the following equation:


$$P = 0.64 \times I_{F(AV)} + 0.0073 I_{F(RMS)}^2$$

## 1.1 Characteristics (curves)


**Figure 1: Average forward power dissipation versus average forward current (per diode)**




**Figure 2: Average forward current versus ambient temperature ( $\delta = 0.5$ , per diode)**




**Figure 3: Normalized avalanche power derating versus pulse duration ( $T_J = 125^\circ\text{C}$ )**




**Figure 4: Relative variation of thermal impedance junction to case versus pulse duration (TO-220AB, D²PAK, TO-247)**




**Figure 5: Relative variation of thermal impedance junction to case versus pulse duration (TO-220FPAB)**




**Figure 6: Reverse leakage current versus reverse voltage applied (typical values, per diode)**




**Figure 7: Junction capacitance versus reverse voltage applied (typical values, per diode)**  
C(pF)



**Figure 8: Forward voltage drop versus forward current (per diode)**



**Figure 9: Thermal resistance junction to ambient versus copper surface under tab for D<sup>2</sup>PAK (typical values)**




## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK® is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Torque values (TO-220AB and TO-220FPAB): 0.55 N·m recommended; 0.7 N·m maximum
- Torque values (TO-247): 0.55 N·m recommended; 1.0 N·m maximum


## 2.1 D<sup>2</sup>PAK package information

Figure 10: D<sup>2</sup>PAK package outline

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 5: D<sup>2</sup>PAK package mechanical data

| Ref. | Dimensions  |       |        |       |
|------|-------------|-------|--------|-------|
|      | Millimeters |       | Inches |       |
|      | Min.        | Max.  | Min.   | Max.  |
| A    | 4.36        | 4.60  | 0.172  | 0.181 |
| A1   | 0.00        | 0.25  | 0.000  | 0.010 |
| b    | 0.70        | 0.93  | 0.028  | 0.037 |
| b2   | 1.14        | 1.70  | 0.045  | 0.067 |
| c    | 0.38        | 0.69  | 0.015  | 0.027 |
| c2   | 1.19        | 1.36  | 0.047  | 0.053 |
| D    | 8.60        | 9.35  | 0.339  | 0.368 |
| D1   | 6.90        | 8.00  | 0.272  | 0.311 |
| D2   | 1.10        | 1.50  | 0.043  | 0.060 |
| E    | 10.00       | 10.55 | 0.394  | 0.415 |
| E1   | 8.10        | 8.90  | 0.319  | 0.346 |
| E2   | 6.85        | 7.25  | 0.266  | 0.282 |
| e    | 2.54 typ.   |       | 0.100  |       |
| e1   | 4.88        | 5.28  | 0.190  | 0.205 |
| H    | 15.00       | 15.85 | 0.591  | 0.624 |
| J1   | 2.49        | 2.90  | 0.097  | 0.112 |
| L    | 1.90        | 2.79  | 0.075  | 0.110 |
| L1   | 1.27        | 1.65  | 0.049  | 0.065 |
| L2   | 1.30        | 1.78  | 0.050  | 0.070 |
| R    | 0.4 typ.    |       | 0.015  |       |
| V2   | 0°          | 8°    | 0°     | 8°    |

Figure 11: D<sup>2</sup>PAK recommended footprint (dimensions in mm)

## 2.2 TO-220AB package information

Figure 12: TO-220AB package outline




Table 6: TO-220AB package mechanical data

| Ref. | Dimensions  |       |                       |        |
|------|-------------|-------|-----------------------|--------|
|      | Millimeters |       | Inches <sup>(1)</sup> |        |
|      | Min.        | Max.  | Min.                  | Max.   |
| A    | 4.40        | 4.60  | 0.1732                | 0.1811 |
| b    | 0.61        | 0.88  | 0.0240                | 0.0346 |
| b1   | 1.14        | 1.70  | 0.0449                | 0.0669 |
| c    | 0.48        | 0.70  | 0.0189                | 0.0276 |
| D    | 15.25       | 15.75 | 0.6004                | 0.6201 |
| D1   | 1.27 typ.   |       | 0.0500 typ.           |        |
| E    | 10.00       | 10.40 | 0.3937                | 0.4094 |
| e    | 2.40        | 2.70  | 0.0945                | 0.1063 |
| e1   | 4.95        | 5.15  | 0.1949                | 0.2028 |
| F    | 1.23        | 1.32  | 0.0484                | 0.0520 |
| H1   | 6.20        | 6.60  | 0.2441                | 0.2598 |
| J1   | 2.40        | 2.72  | 0.0945                | 0.1071 |
| L    | 13.00       | 14.00 | 0.5118                | 0.5512 |
| L1   | 3.50        | 3.93  | 0.1378                | 0.1547 |
| L20  | 16.40 typ.  |       | 0.6457 typ.           |        |
| L30  | 28.90 typ.  |       | 1.1378 typ.           |        |
| ØP   | 3.75        | 3.85  | 0.1476                | 0.1516 |
| Q    | 2.65        | 2.95  | 0.1043                | 0.1161 |

**Notes:**<sup>(1)</sup>Inch dimensions are for reference only.

## 2.3 TO-220FPAB package information

Figure 13: TO-220FPAB package outline




Table 7: TO-220FPAB package mechanical data

| Ref. | Dimensions  |       |             |        |
|------|-------------|-------|-------------|--------|
|      | Millimeters |       | Inches      |        |
|      | Min.        | Max.  | Min.        | Max.   |
| A    | 4.40        | 4.60  | 0.1739      | 0.1818 |
| B    | 2.5         | 2.7   | 0.0988      | 0.1067 |
| D    | 2.50        | 2.75  | 0.0988      | 0.1087 |
| E    | 0.45        | 0.70  | 0.0178      | 0.0277 |
| F    | 0.75        | 1.0   | 0.0296      | 0.0395 |
| F1   | 1.15        | 1.70  | 0.0455      | 0.0672 |
| F2   | 1.15        | 1.70  | 0.0455      | 0.0672 |
| G    | 4.95        | 5.20  | 0.1957      | 0.2055 |
| G1   | 2.40        | 2.70  | 0.0949      | 0.1067 |
| H    | 10.00       | 10.40 | 0.3953      | 0.4111 |
| L2   | 16.00 typ.  |       | 0.6324 typ. |        |
| L3   | 28.60       | 30.60 | 1.1304      | 1.2095 |
| L4   | 9.80        | 10.6  | 0.3874      | 0.4190 |
| L5   | 2.90        | 3.60  | 0.1146      | 0.1423 |
| L6   | 15.90       | 16.40 | 0.6285      | 0.6482 |
| L7   | 9.00        | 9.30  | 0.3557      | 0.3676 |
| Dia  | 3.0         | 3.20  | 0.1186      | 0.1265 |

## 2.4 TO-247 package information

Figure 14: TO-247 package outline




Table 8: TO-247 package mechanical data

| Ref.              | Dimensions  |       |       |        |       |       |
|-------------------|-------------|-------|-------|--------|-------|-------|
|                   | Millimeters |       |       | Inches |       |       |
|                   | Min.        | Typ.  | Max.  | Min.   | Typ.  | Max.  |
| A                 | 4.85        |       | 5.15  | 0.191  |       | 0.203 |
| A1                | 2.20        |       | 2.60  | 0.086  |       | 0.102 |
| b                 | 1.00        |       | 1.40  | 0.039  |       | 0.055 |
| b1                | 2.00        |       | 2.40  | 0.078  |       | 0.094 |
| b2                | 3.00        |       | 3.40  | 0.118  |       | 0.133 |
| c                 | 0.40        |       | 0.80  | 0.015  |       | 0.031 |
| D <sup>(1)</sup>  | 19.85       |       | 20.15 | 0.781  |       | 0.793 |
| E                 | 15.45       |       | 15.75 | 0.608  |       | 0.620 |
| e                 | 5.30        | 5.45  | 5.60  | 0.209  | 0.215 | 0.220 |
| L                 | 14.20       |       | 14.80 | 0.559  |       | 0.582 |
| L1                | 3.70        |       | 4.30  | 0.145  |       | 0.169 |
| L2                |             | 18.50 |       |        | 0.728 |       |
| ØP <sup>(2)</sup> | 3.55        |       | 3.65  | 0.139  |       | 0.143 |
| ØR                | 4.50        |       | 5.50  | 0.177  |       | 0.217 |
| S                 | 5.30        | 5.50  | 5.70  | 0.209  | 0.216 | 0.224 |

**Notes:**

<sup>(1)</sup>Dimension D plus gate protusion does not exceed 20.5 mm

<sup>(2)</sup>Resin thickness around the mounting hole is not less than 0.9 mm.

### 3 Ordering information

Table 9: Ordering information

| Order code     | Marking      | Package            | Weight | Base qty | Delivery mode |
|----------------|--------------|--------------------|--------|----------|---------------|
| STPS30150CT    | STPS30150CT  | TO-220AB           | 1.95g  | 50       | Tube          |
| STPS30150CFP   | STPS30150CFP | TO-220FPAB         | 1.9g   | 50       | Tube          |
| STPS30150CW    | STPS30150CW  | TO-247             | 4.4g   | 30       | Tube          |
| STPS30150CG-TR | STPS30150CG  | D <sup>2</sup> PAK | 1.38g  | 1000     | Tape and reel |

### 4 Revision history

Table 10: Document revision history

| Date        | Revision | Changes                                                                                                                                                                                                                                                                                                     |
|-------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Feb-2004    | 7        | Previous release                                                                                                                                                                                                                                                                                            |
| 26-Nov-2010 | 8        | Added ECOPACK statement. Corrected package name in <i>Figure 12</i> .                                                                                                                                                                                                                                       |
| 16-May-2017 | 9        | Updated features and package silhouettes in cover page.<br>Updated <a href="#">Section 1: "Characteristics"</a> , <a href="#">Section 1.1: "Characteristics (curves)"</a> , <a href="#">Section 2: "Package information"</a> and <a href="#">Section 3: "Ordering information"</a> .<br>Minor text changes. |

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics – All rights reserved