






1		2		3		4		5																																																							
						TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PBT FLAMABILITY RATING: UL94-V0 COLOR: BLACK CONTACT MATERIAL: COPPER ALLOY CONTACT TYPE: STAMPED CONTACT PLATING: GOLD QUALITY CLASS: 3 AS PER CECC 75 301-802 PITCH: 2.54MM ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO 125°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL CURRENT RATING: 3A MAX WORKING VOLTAGE: 250V AC INSULATOR RESISTANCE: >1000 MOHM DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/MN CONTACT RESISTANCE: 20 mOHM MAX STANDARD  CERTIFIED: E323964 / MODEL NUMBER 612-212-R SOLDERING WAVE PROCESS ONLY PACKAGING TRAY DIMENSION <table><tr><th>No. of Positions</th><th>Dim A</th><th>Dim B</th><th>No. of Positions</th><th>Dim A</th><th>Dim B</th></tr><tr><td>6</td><td>26.92</td><td>5.08</td><td>26</td><td>52.30</td><td>30.48</td></tr><tr><td>8</td><td>29.46</td><td>7.62</td><td>30</td><td>57.40</td><td>35.56</td></tr><tr><td>10</td><td>32.00</td><td>10.16</td><td>34</td><td>62.50</td><td>40.64</td></tr><tr><td>12</td><td>34.54</td><td>12.70</td><td>40</td><td>70.10</td><td>48.26</td></tr><tr><td>14</td><td>37.08</td><td>15.24</td><td>50</td><td>82.85</td><td>60.96</td></tr><tr><td>16</td><td>39.62</td><td>17.78</td><td>60</td><td>95.50</td><td>73.66</td></tr><tr><td>20</td><td>44.70</td><td>22.86</td><td></td><td></td><td></td></tr><tr><td>24</td><td>49.78</td><td>27.94</td><td></td><td></td><td></td></tr></table>				No. of Positions	Dim A	Dim B	No. of Positions	Dim A	Dim B	6	26.92	5.08	26	52.30	30.48	8	29.46	7.62	30	57.40	35.56	10	32.00	10.16	34	62.50	40.64	12	34.54	12.70	40	70.10	48.26	14	37.08	15.24	50	82.85	60.96	16	39.62	17.78	60	95.50	73.66	20	44.70	22.86				24	49.78	27.94			
No. of Positions	Dim A	Dim B	No. of Positions	Dim A	Dim B																																																										
6	26.92	5.08	26	52.30	30.48																																																										
8	29.46	7.62	30	57.40	35.56																																																										
10	32.00	10.16	34	62.50	40.64																																																										
12	34.54	12.70	40	70.10	48.26																																																										
14	37.08	15.24	50	82.85	60.96																																																										
16	39.62	17.78	60	95.50	73.66																																																										
20	44.70	22.86																																																													
24	49.78	27.94																																																													
		Recommended P.C.B Layout																																																													
Notes: No. of Positions 64 with three key; Other positions with one key																																																															
RoHS Compliant				PROJECTION: 		GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15																																																									
G	30-AUG-12	DIM	GG	APPROVAL: RJ		UNIT: MM		DESCRIPTION: 2.54MM MALE ANGLED BOX HEADER WITH SHORT LEVER		SIZE A4																																																					
F	07-MAR-12	DRAWING	GG			SCALE:		WERI PART NO: 612 0xx 221 21																																																							
E	08-JUL-10	PACKAGING	JC																																																												
D	15-MAR-10	DELETE NOTES	JP																																																												
C	16-NOV-09	STANDARD	JP																																																												
I	19-MAR-13	NOTES	AR																																																												
H	20-FEB-13	Overall Length	QL																																																												
REV	DATE	FILE	BY			DRAW: MIKE																																																									

