




LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	L		REV PER 063C-0104-01	04SEP01	RB JO
		L1		REVISED PER ECO-09-021510	14SEP09	KK AEG

1. RECEPTACLE ACCEPTS AN .008-.014 THK. I.C. LEAD.
2. TWO .000030 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI






SECTION A-A

ROTATED 90° CW
SCALE 10:1
FOR -8, -7 & -6 ONLY



SECTION A-A

ROTATED 90° CW
SCALE 10:1
FOR -1, -2 & -3 ONLY



RECOMMENDED MOUNTING HOLE PATTERN

OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-8
	△	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-7
OBSOLETE	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-6
OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-4
	△	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-3
OBSOLETE	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-2
	△	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643653-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.CYRUS 01JUNE84	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
			CHK N.JONES 03JULY84	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.GRAY 10JULY84	NAME SOCKET ASSY, SIP, 21 POS, DIPLOMATE DL -
		0 PLC ± -	PRODUCT SPEC	
		1 PLC ± -	108-1066	
		2 PLC ± -	APPLICATION SPEC	
MATERIAL SEE TABLE		3 PLC ± .005	114-1049	SIZE A1
		4 PLC ± -	WEIGHT -	
		ANGLES ± 1°	CUSTOMER DRAWING	SCALE 5:1
		FINISH SEE TABLE	RESTRICTED TO -	SHEET 1 OF 1
			REV L1	