

4




3

2


1

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
SEP 2007
ALL RIGHTS RESERVED.


LOC J	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D1	REVISED PER ECR—20—005200	08APR2020	D.Z	S.L



- (APPLIED TO SHEET 1-2)
1. MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC UL94V-0
COLOR: SEE TABLE
CONTACT: COPPER ARROY
LOCK LEVER: STAINLESS STEEL
PEG: COPPER ARROY
- 2-1. FINISH ; CONTACT AREA: GOLD FLASH
ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.
- 2-2. FINISH ; CONTACT AREA: 0.000254MIN GOLD
ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.
- 2-3. FINISH ; CONTACT AREA: 0.00076MIN GOLD
ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.
- △ COPLANARITY: 0.1 MAX. (BEFORE SOLDERING)
△ THE FLOATING VALUE BY SOLDERING IS NOT INCLUDED.
△ NOT MATING CONDITION.
6. IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.



GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ > 10 : ±0.25
100 ≥ > 30 : ±0.3
ANGLES : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.FUMIKURA 18SEP2007	TE Connectivity				
		CHK K.IKEGAMI 18SEP2007					
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K.IKEGAMI 18SEP2007	NAME				
	0 PLC ±	PRODUCT SPEC	DDR3 SODIMM SOCKET 0.6mm PITCH 204POS 9.2mm HEIGHT STANDARD TYPE				
	1 PLC ±	108-78493					
	2 PLC ±	APPLICATION SPEC					
	3 PLC ±						
	4 PLC ±						
	ANGLES ±						
MATERIAL	FINISH	WEIGHT 6.2g	SIZE A3		CAGE CODE 00779	DRAWING NO C-2013310	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 2:1		SHEET 1 OF 6		REV D1

4

3


2


1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION , .SEP 2007
© COPYRIGHT 2007 By – ALL RIGHTS RESERVED.	

LOC J	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-3	1.5V	204	4-2013310-3
AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-3	1.5V	204	2-2013310-3
AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-2	1.5V	204	2-2013310-2
AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-1	1.5V	204	2-2013310-1
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-3	1.5V	204	2013310-3
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-2	1.5V	204	2013310-2
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-1	1.5V	204	2013310-1
TOOLING STATUS	PACKAGING TYPE	REMARK	HOUSING COLOR	FINISH	POWER SUPPLY	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity				
		CHK					
		APVD					
		PRODUCT SPEC					
NAME		DDR3 SODIMM SOCKET 0.6mm PITCH 204POS 9.2mm HEIGHT STANDARD TYPE					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		A300779		C-2013310	—
MATERIAL				WEIGHT			
CUSTOMER DRAWING				SCALE	SHEET		REV
				2:1		2 OF 6 D1	




(APPLIED TO SHEET 5)

1. THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.
2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$



B-B
SCALE 1:1



CUSTOMER DRAWING

- 2013310-
PART NO.



TE Connectivity

DDR3 SODIMM SOCKET
0.6mm PITCH 204POS
2mm HEIGHT STANDARD TYPE

9 | C-2013310

RESTRICTED TO

REV D1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, .SEP 2007

ALL RIGHTS RESERVED.

© COPYRIGHT 2007 By —

LOC
JDIST
/

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

(400mm MIN.)

END SECTION W/ PRODUCT CHARGE
(EMPTY)
(10 pockets Min.)LEADING SECTION
(20 pockets Min.)




SEE DETAIL X

TOP COVER TAPE

PULL OUT DIRECTION

(APPLIED TO SHEET 6)


1. THE DIRECTION OF EACH CONNECTOR ON A EMBOSS IS REFERRED TO THIS DRAWING.
2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	± 0.5
ANGLES	$\pm 3^\circ$

FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

150EA
QTY/REEL*—2013310—*
PART NO.**STE**

TE Connectivity

NAME

DDR3 SODIMM SOCKET
0.6mm PITCH 204POS
9.2mm HEIGHT STANDARD TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C—2013310

SCALE 1:2

SHEET 6 OF 6

REV D1