

**Part Number: 85056-9000**

DINCONN. M REV. FEM. 24+8 WITH CLIP

*Image not available*

Status:

Planned for Obsolescence

[CHECK DISTRIBUTOR INVENTORY](#)

Series:

[85056](#)

Category:

Molex Parts

[Add to My Parts](#)[Go to Part Detail ▾](#)*Series image - Reference only***Specifications & Other Documents:***Documents not available online***Sales Drawings, 3D Models, and Brochures**

Drawing (PDF)

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](http://www.molex.com)**Product Environmental Compliance**Questions on Product Environmental Compliance? Email [productcompliance@molex.com](mailto:productcompliance@molex.com)[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#): Contains SVHC: No[Low-Halogen Status](#): Not Low-Halogen**Application Tooling**[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)**Part Detail**[COLLAPSE ALL](#)**▼ General**

Status	Planned for Obsolescence
Category	Molex Parts
Series	<a href="#">85056</a>
UPC	800756529226

**▼ Physical**

Flammability	94V-0
Net Weight	10.061/g

**▼ Agency Certification**

CSA	LR19980
UL	E29179

**▼ Material Info****Molex Connectors**

Wire-to-Board

Board-to-Board

Wire-to-Wire

Input/Output (IO)

FFC/FPC

Sockets

**Other Products**

Fiber Optic Products

Antennas

Industrial Automation

Membrane Switches

Copper Flex

PCB Assemblies

Woodhead Electrical

Solid State Lighting

**Resources**

Catalog

Cross-Reference

Industries

Literature

Product Name

**Company Info**

About Us

Careers

Contact Us

ecocare

Investors

Press Room

Shows &amp; Events

**Other Info**

Feedback

Help

Legal Disclaimer

Privacy Policy

Sitemap

**Stay Connected with Molex:**