






REV.	DATE	DESCRIPTION
NC	05/22/03	INITIAL RELEASE
A	10/24/06	ADD "50ohm" TO DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .187"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex BNC CRIMP PLUG – 50ohm (WEST PENN MINI MAX 500 CABLE)											
8						DRAWN	G.R.S.								10/24/06	PART DESCRIPTION			
7						CHECKED													
6	FERRULE	COPPER	NICKEL	1			ISSUED			PART NO.									
5	SLEEVE	DELRIN	NATURAL	1			SHEET	1 OF 1						112537					
4	GASKET	RUBBER	RED	1					DWG. NO. 112537.DWG REV. A SIZE A SCALE NA										
3	INSULATOR	DELRIN	NATURAL	1															
2	CONTACT PIN	BRASS	GOLD	1															
1	SHELL/BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE	C:/112/112537.DWG											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112537](#)