





SIZE	STYLE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]	E BSC.
E09	PIN	1.213 [30.81]	-----	.666[16.92]	.984 [24.99]	.432 [10.97]
	SOCKET		.643[16.33]	-----		
A15	PIN	1.541 [39.14]	-----	.994[25.25]	1.312 [33.32]	.756 [19.20]
	SOCKET		.971[24.66]	-----		
B25	PIN	2.088 [53.04]	-----	1.534[38.96]	1.852 [47.04]	1.304 [33.12]
	SOCKET		1.511[38.38]	-----		
C37	PIN	2.729 [69.32]	-----	2.182[55.42]	2.500 [63.50]	1.956 [49.68]
	SOCKET		2.159[54.84]	-----		

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.



ORDERING CODE: F C C 1 7 - E O 9 P C - 4 4 0 G

SERIES _____

SIZE/NUMBER OF CONTACTS

E09, A15, B25, OR C37

CONNECTOR STYLE

CONCLUSION
P=PIN

TERMINATION TYPE

C=.590"[14.99] FOOTPRINT

MOUNTING

2=.120[3.05] DIA THROUGH HOLE

3=#4-40 UNC SELF-LOCKING THREAD

4-#4-40 UNC THREAD
6-#3-48 UNC THREAD


6=M3 x 0.5 THREAD
E-CODE 4 MOUNTING WITH #4

E-CODE 4 MOUNTING WITH #4-48 UNC
HEX JACK SOCKET SUPPLIED.

F-#4-40 UNC THREAD

0.187[4.75] FIXED JACK SOCKET

CODE "F" MOUNTING OPTION



NOTES:

1. MATERIALS: - SHELLS - TIN PLATED STEEL
 - CONTACTS - PHOSPHOR BRONZE PLATED WITH GOLD OVER NICKEL ON THE MATING AREA AND TIN-LEAD ON THE TERMINALS
 - INSULATOR - ENGINEERING THERMOPLASTIC, FLAMMABILITY RATING UL94V-0, BLACK.
2. CONTACT RESISTANCE: 15 MILLIOHMS MAXIMUM.
3. INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
4. CURRENT RATING: 5 AMPS MAXIMUM
2 AMPS FILTERING MAXIMUM
5. OPERATING TEMPERATURE: -40°C TO 85°C.
6. TOLERANCE, UNLESS INDICATED OTHERWISE, ±.005 [0.13].

MATERIAL -----	DRAWN <i>I.ESSAJEE</i>	DATE <i>26/01/19</i>	Amphenol Canada Corp. TITLE <i>FCC17 FILTERED D-SUB, RIGHT ANGLE .590"[14.99] F/P, PIN & SOCKET - PLASTIC MTG. BRACKET & BOARDLOCK</i>				
	DESIGNED <i>K.LAMBIE</i>	<i>26/01/19</i>					
	CHECKED						
	I. E. APPRD.						
FINISH -----	Q. A. APPRD.		DWG	DRAWING NO. <i>P-FCC17-XXXXC-XX0X</i>	REV <i>B</i>		
	DWG. APPRD.						
	ENG. REL. NO.						
	REF.						
	DIMENSIONS ARE IN INCHES <i>[mm]</i>	CODE ID. NO. <i>03554</i>					
	SCALE <i>N.T.S.</i>					WT. <i>-----</i>	SURF. <i>-----</i>