







LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	APVD
GP	00	B1		REVISED PER ECO-11-005033	26MAR11	RK HMR

- △ HOUSING—MATERIAL : LIQUID—CRYSTAL—POLYMER, COLOR: NATURAL.
- △ CONTACT—MATERIAL : PHOS. BRONZE.
- △ LATCH—MATERIAL : BRASS, NICKEL PLATE
- △ CONTACT—PLATE: 0.00508[.000200] MIN MATTE TIN OVER 0.00127[.000050] MIN NICKEL.
5. IN ADDITION TO THOSE RECOMMENDED "SIMM" P.C. BOARD DIMENSIONS AND TOLERANCES SHOWN, ALL JEDEC SPECIFICATIONS APPLY AS SHOWN ON MO-116, ISSUE A.
6. RECOMMENDED MATING S.I.M.M. TAB METALLURGY:
BASE METAL—COPPER. PLATING TO BE 0.00762[.000300] MIN TIN/LEAD OVER 0.00127[.000050] MIN NICKEL.
- △ DATE CODE: (YEAR WEEK) XXXX FORMAT, LOCATED APPROXIMATELY AS SHOWN ON OPPOSITE SIDE.



118.11[4.650]	111.35[4.384]	60.96[2.400]	49.53[1.950]	125.73[4.950]	105.41[4.150]	80	5822021-5
107.95[4.250]	101.19[3.984]	55.88[2.200]	44.45[1.750]	115.57[4.550]	95.25[3.750]	72	5822021-4
F	E	D	C	B	A	NO. OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WAITMAN CHK M. YEOMANS	5/JAN/05 5/JAN/05	 TE Connectivity	
DIMENSIONS: mm [INCHES]		APVD M. YEOMANS	5/JAN/05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		CONNECTOR, MICRO-EDGE, .050, VERTICAL, TIN PLATE, METAL LATCH	
0 PLC ± -		PRODUCT SPEC			
1 PLC ± -		APPLICATION SPEC			
2 PLC ± 0.13[.005]		—			
3 PLC ± -		—		SIZE CAGE CODE DRAWING NO	
4 PLC ± -		—		A1 00779 C-5822021	
ANGLES ± -		—		RESTRICTED TO	
MATERIAL		FINISH		—	
				CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 OF 1 REV B1	