


MG17450WB-BN4MM

RoHS



Features

- IGBT³ CHIP(1700V Trench+Field Stop technology)
- Low turn-off losses, short tail current
- $V_{CE(sat)}$ with positive temperature coefficient
- DIODE CHIP(1700V EMCON 3 technology)
- Free wheeling diodes with fast and soft reverse recovery

Applications

- AC motor control
- Motion/servo control
- Photovoltaic/Fuel cell
- Inverter and power supplies

Module Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Parameters	Test Conditions	Min	Typ	Max	Unit
$T_{J\max}$	Max. Junction Temperature				150	$^\circ\text{C}$
T_{Jop}	Operating Temperature		-40		125	$^\circ\text{C}$
T_{stg}	Storage Temperature		-40		125	$^\circ\text{C}$
V_{isol}	Insulation Test Voltage	AC, t=1min		3500		V
CTI	Comparative Tracking Index		250			
Torque	Module-to-Sink	Recommended (M5)	2.5		5	N·m
Torque	Module Electrodes	Recommended (M6)	3		5	N·m
Weight				350		g

Absolute Maximum Ratings ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Parameters	Test Conditions	Values	Unit
IGBT				
V_{CES}	Collector - Emitter Voltage	$T_J = 25^\circ\text{C}$	1700	V
V_{GES}	Gate - Emitter Voltage		± 20	V
I_C	DC Collector Current	$T_C = 25^\circ\text{C}$	600	A
		$T_C = 80^\circ\text{C}$	450	A
I_{CM}	Repetitive Peak Collector Current	$t_p = 1\text{ms}$	900	A
P_{tot}	Power Dissipation Per IGBT		2250	W
Diode				
V_{RRM}	Repetitive Reverse Voltage	$T_J = 25^\circ\text{C}$	1700	V
$I_{F(AV)}$	Average Forward Current	$T_C = 25^\circ\text{C}$	450	A
		$T_C = 80^\circ\text{C}$	350	A
I_{FRM}	Repetitive Peak Forward Current	$t_p = 1\text{ms}$	900	A
I^2t		$T_J = 125^\circ\text{C}$, $t = 10\text{ms}$, $V_R = 0\text{V}$	20000	A^2s

Power Module

1700V 450A IGBT Module

Electrical and Thermal Specifications ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Parameters	Test Conditions	Min	Typ	Max	Unit
IGBT						
V _{GE(th)}	Gate - Emitter Threshold Voltage	V _{CE} =V _{GE} , I _C =18mA	5.0	5.8	6.4	V
V _{CE(sat)}	Collector - Emitter	I _C =450A, V _{GE} =15V, T _J =25°C		2.0	2.45	V
	Saturation Voltage	I _C =450A, V _{GE} =15V, T _J =125°C		2.4		V
I _{CES}	Collector Leakage Current	V _{CE} =1700V, V _{GE} =0V, T _J =25°C			3	mA
		V _{CE} =1700V, V _{GE} =0V, T _J =125°C			20	mA
I _{GES}	Gate Leakage Current	V _{CE} =0V, V _{GE} =±15V, T _J =125°C	-400		400	nA
R _{Gint}	Integrated Gate Resistor			1.7		Ω
Q _{ge}	Gate Charge	V _{CE} =900V, I _C =450A , V _{GE} =±15V		5.1		μC
C _{ies}	Input Capacitance	V _{CE} =25V, V _{GE} =0V, f =1MHz		40.5		nF
C _{res}	Reverse Transfer Capacitance			1.3		nF
t _{d(on)}	Turn - on Delay Time	V _{CC} =900V I _C =450A R _G =3.3Ω V _{GE} =±15V Inductive Load	T _J =25°C		280	ns
			T _J =125°C		300	ns
t _r	Rise Time		T _J =25°C		80	ns
			T _J =125°C		100	ns
t _{d(off)}	Turn - off Delay Time		T _J =25°C		810	ns
			T _J =125°C		1000	ns
t _f	Fall Time		T _J =25°C		180	ns
			T _J =125°C		300	ns
E _{on}	Turn - on Energy		T _J =25°C		96.5	mJ
			T _J =125°C		140	mJ
E _{off}	Turn - off Energy		T _J =25°C		96	mJ
			T _J =125°C		140	mJ
I _{SC}	Short Circuit Current	t _{psc} ≤10μS , V _{GE} =15V; T _J =125°C , V _{CC} =1000V		1800		A
R _{thJC}	Junction-to-Case Thermal Resistance (Per IGBT)				0.055	K/W
Diode						
V _F	Forward Voltage	I _F =450A, V _{GE} =0V, T _J =25°C		1.8	2.2	V
		I _F =450A, V _{GE} =0V, T _J =125°C		1.9		V
I _{RRM}	Max. Reverse Recovery Current	I _F =450A, V _R =900V di _F /dt=-4500A/μs T _J =125°C		570		A
Q _{rr}	Reverse Recovery Charge			195		μC
E _{rec}	Reverse Recovery Energy			110		mJ
R _{thJCD}	Junction-to-Case Thermal Resistance (Per Diode)				0.10	K/W

NTC Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

Symbol	Parameters	Test Conditions	Min	Typ	Max	Unit
R_{25}	Resistance	$T_c=25^\circ\text{C}$		5		K Ω
$B_{25/50}$				3375		K

Figure 1: Typical Output Characteristics for IGBT Inverter




Figure 2: Typical Output Characteristics for IGBT Inverter




Figure 3: Typical Transfer Characteristics for IGBT Inverter




Figure 4: Switching Energy vs. Gate Resistor for IGBT Inverter




Figure 5: Switching Energy vs. Collector Current for IGBT Inverter




Figure 6: Reverse Biased Safe Operating Area for IGBT Inverter




Figure 7: Diode Forward Characteristics for Diode Inverter




Figure 8: Switching Energy vs. Gate Resistort for Diode Inverter




Figure 9: Transient Thermal Impedance of Diode and IGBT Inverter






Figure 10: NTC Characteristics



Circuit Diagram



Technical drawing of a mechanical part, likely a bracket or support, showing front, top, and side views with dimensions in millimeters.

Front View Dimensions:

- Overall length: 62.00
- Overall width: 20.84±0.5
- Mounting hole diameter: 17.9±0.5
- Mounting hole position from left edge: 12.50, 12.10, 2.50
- Mounting hole position from right edge: 17.9±0.5, 20.84±0.5

Top View Dimensions:

- Overall length: 62.00
- Overall width: 20.84±0.5
- Mounting hole diameter: 17.9±0.5
- Mounting hole position from left edge: 12.50, 12.10, 2.50
- Mounting hole position from right edge: 17.9±0.5, 20.84±0.5

Side View Dimensions:

- Overall height: 12.50
- Mounting hole diameter: 17.9±0.5
- Mounting hole position from top edge: 12.10, 2.50

Detail View A2:1

Detail view A2:1 shows a cross-section of the mounting hole with dimensions:

- Overall diameter: 17.9±0.5
- Inner diameter: 12.10
- Outer diameter: 2.50

Packing Options

Part Numbering System

