











PRODUCT NO  
SEE TABLE

REV	DESCRIPTION	REV'D BY	DATE
AF	ECR S50036	BS LOW	25FEB95
AG	ECR S50156	BS LOW	22JUL95
AH	ECR S70311	BS LOW	04NOV97
AJ	ECR S80047	BS LOW	19FEB98
AK	ECR S80136	BS LOW	01JUNE98







CUSTOMER COPY

GEN. TOLERANCES		DO NOT SCALE DWG.		
REFER TO NOTE 2				
		 		
				DESCRIPTION
		NAME	DATE	MINITEK II HIGH PROFILE STR HDR
DRAWN		BS LOW	01JUNE98	
CHECKED			01JUN98	
APPROVED			1.6.98	PRODUCT NO. 87715
				SCALE SHT 1 OF 3

PRODUCT NO	POS	DIM F	DIM G	DIM X	DIM Y	'KINK' POS	POL. POS	PLATING	DESCRIPTION	REV
87715-X01	2X16	4.0	2.5	30	32	-	-	0	0.2 um Au	AF
-X02	2X25	4.0	1.5	48	50	-	-	1	0.76 um Au	AG
-X03	2X15	4.0	2.5	28	30	-	-	2	UNASSIGNED	AH
-X04	2X12	4.0	2.5	22	24	-	-	3	0.38 um Au	AJ
-X05	2X13	4.0	2.5	24	26	-	-	4	UNASSIGNED	AK
-X06	2X4	4.0	3.0	6	8	-	-	5	0.38 um GXT	
-X07	2X7	3.7	3.1	12	14	-	-	6	0.76 um GXT	
-X08	2X8	3.7	3.1	14	16	-	-			
-X09	2X10	15.5	2.5	18	20	-	-			
-X10	2X10	5.5	2.4	18	20	-	-			
-X11	2X3	4.0	2.0	4	6	-	-			
-X12	2X8	10.0	2.5	14	16	-	-			
-X13	2X20	4.0	2.5	38	40	-	-			
-X14	2X10	6.2	2.5	18	20	9,10,11,12	-			
-X15	2X12	6.2	2.5	22	24	11,12,13,14	-			
-X16	2X7	4.0	2.5	12	14	-	-			
-X17	2X11	4.0	2.5	20	22	-	-			
-X18	2X10	3.7	2.0	18	20	-	-			
-X19	2X5	4.0	3.0	8	10	-	-			
-X20	2X19	4.0	3.0	36	38	-	-			
-X21	2X9	4.0	3.0	16	18	-	-			
-X22	2X18	4.0	3.0	34	36	-	-			
-X23	2X10	4.0	2.0	18	20	9,10,11,12	-			
-X24	2X5	4.0	2.0	8	10	-	-			
-X25	2X25	4.0	2.3	48	50	-	-			
-X26	2X25	4.0	2.3	48	50	-	26			
-X27	2X9	5.0	2.5	16	18	-	-			
-X28	2X12	5.0	2.5	22	24	-	-			

GEN. TOLERANCES		DO NOT SCALE DWG.		
REFER TO NOTE 2				
		 		
	NAME	DATE		DESCRIPTION MINITEK II HIGH PROFILE STR HDR
DRAWN	BS LOW	01JUNE98		
CHECKED	<i>[Signature]</i>	01JUN98		
APPROVED	<i>[Signature]</i>	1.6.98		PRODUCT NO. 87715 SCALE SHT 2 OF 3

CUSTOMER COPY

PRODUCT NO	POS	DIM F	DIM G	DIM X	DIM Y	'KINK' POS	POL. POS
87715-X29	2X10	4,0	1,3	18	20	-	-
-X30	2X12	3,5	3,5	22	24	-	-
-X31	2X22	5,0	2,3	42	44	-	-
-X32	2X13	4,0	4,0	24	26	-	26

REV
AF
AG
AH
AJ
AK

#### PART NUMBER INFORMATION

XXXXX-XXX

BASE P/N ———— TERMINAL PLATING

#### NOTES

##### 1 MATERIAL

BODY : GLASS FILLED NYLON UL 94V-0 BLACK

PIN : PHOSPHOR BRONZE

##### 2 GENERAL TOLERANCE $\pm 0.25$

##### ③ DIM 1,0 APPLIES TO MOLDED SIDE(S) ONLY. IF

SIDE(S) ARE SAW, DIM 0,5 MIN APPLIES.

##### ④ RECESS APPLIES TO MOLDED SIDE(S) ONLY.

##### ⑤ 'KINKING' FEATURE OPTIONAL. REFER TO TABLE FOR 'KINK' POSITIONS.

##### ⑥ POLARISED BY OMISSION OF PINS. REFER TO TABLE FOR POLARISED POS.










FIG. 1  
NOTE ⑤

CUSTOMER COPY

GEN. TOLERANCES		DO NOT SCALE DWG.			
REFER TO NOTE 2		  			
	NAME	DATE	DESCRIPTION  MINITEK II HIGH PROFILE STR HDR		
DRAWN	BS LOW	01JUNE98			
CHECKED		01JUN 98			
APPROVED		1.6.98			
			PRODUCT NO.	87715	
			SCALE	SHT <u>3</u> OF <u>3</u>	