


Data Sheet


Type Number 6430
Designation IEC CR 2430
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 300 mAh
 Load 5.6 kOhm, at 20°C down to 2 V

Weight (approx.) 4 g
Volume 1,3 ccm
Coding..... Date of Manufacturing Month/Year

Temperature Ranges	min	max.
Storage	-55°C	70°C
Discharge	-20°C	70°C*

Dimensions	min	max.
Diameter (A)	24,20	24,50
Height (B)	2,70	3,00
Shoulder Diameter[E].....	16,30	16,70

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d, 7d/w	5600 Ω	Time: Capacity [mAh]: Energy [mWh]:	600h 300 840

* Contact VARTA if the application is intended to be outside the range of -20°C to +70°C.

Information and contents in this data sheet are for reference purpose only.
 They do not constitute any warranty or representation and are subject to change without notice.
 For most current information and further details, please contact your VARTA representative.

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst

Subject to change without prior notice!


Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Date of issue: 2014-09-16


Data Sheet

Performance Data:

- Temperature Characteristics***




- Operating Voltage vs. load resistance***



*Discharge depth 40%

- Capacity vs. load resistance**



- Self-discharge rate < 1% at room temperature
- Storage life > 10 years
- Operating life* > 10 years

* depending on environmental conditions and energy consumption

*Information and contents in this data sheet are for reference purpose only.
They do not constitute any warranty or representation and are subject to change without notice.
For most current information and further details, please contact your VARTA representative.*

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst

Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Date of issue: 2014-09-16

Subject to change without prior notice!