



DIMENSIONS:

A	3.125" ±0.063
B	3.436" ±0.125
C	3.796" ±0.063
D	2.500" ±0.063
E	2.188" ±0.063
G	0.203" x 0.400" ±0.015



NOTE: ALL LEADS 8" OUT MIN.



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 240V, 60Hz, BLU - BRN	9.3mA	Max.
Sec. N.L.V	@ 240V, 60Hz, BLU - BRN		
	BLU - RED = RED - BRN =	120.0V	±2%
	BLK - ORG =	5.958V	±2%
	BLK - GRN =	8.342V	±2%
	BLK - YEL =	11.44V	±2%
	BLK - BLK/YEL =	48.62V	±2%
	BLK - RED/YEL =	65.54V	±2%
DCR	@ 20°C, BLU - RED =	56.93 Ω	±20%
	@ 20°C, RED - BRN =	60.95 Ω	±20%
	@ 20°C, BLK - ORG =	0.259 Ω	±20%
	@ 20°C, BLK - GRN =	0.364 Ω	±20%
	@ 20°C, BLK - YEL =	0.498 Ω	±20%
	@ 20°C, BLK - BLK/YEL =	6.727 Ω	±20%
	@ 20°C, BLK - RED/YEL =	9.550 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2000V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	08/13/13	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181		FAX # (519) 886-9540	
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: 1650G	DWG. NO.
			DATE: 08/13/13	APP'D. BY:	TRANSFORMER	1650G
				DIMENSIONS: IN(X) MM()		