

SUBCON-PLUS-CAN/AX

Order No.: 2306566



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2306566>

SUB-D connector, 9-pos., with axial cable entry

CANopen

SafetyBUS p

Commercial data

EAN	4017918962906
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.0401 KG
Catalog page information	Page 553 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
03/23/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	60 V AC/DC
Nominal current I_N	1 A
Bus system	CAN, CANopen, SafetyBus-P
Insertion/withdrawal cycles	> 200
Max. cable diameter	8.4 mm


Min. cable diameter	7.6 mm
SUBCON fixing screws	4-40 UNC
Tightening torque	0.4 Nm
Ambient temperature (operation)	-20 °C ... 75 °C
Housing material	ABS, metal-plated
Pin assignment	2,3,7,9
Width	17 mm
Height	58.2 mm
Length	31.5 mm

Connection data

Connection	D-SUB connection
Number of positions	9
Type of connection	D-SUB socket
Connection	PCB connection
Type of connection	Screw connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Stripping length	5 mm
Tightening torque	0.4 Nm

Diagrams/Drawings

Dimensioned drawing



SUBCON-PLUS-PROFIB/CAN/AX dimensional drawing

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;