



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AJ	16		B	REV PER ECO 08-009474	7/22/2008	JL





RECOMMENDED PCB LAYOUT




RECOMMENDED PANEL CUTOUT

- 1 BRASS PER ASTM-B-16
- 2 BRASS PER ASTM-B-453
- 3 PHOSPHOR BRONZE PER ASTM-B-103
- 4 POLYESTER PBT PER MIL-M-25419, TYPE GPT-15F, UL94V-0 RATED, COLOR: BLACK
- 5 POLYMETHYLPENTENE: GENERAL PURPOSE
- 6 ZINC DIE CAST PER QQ-Z-363
- 7 GOLD PLATE PER ASTM-B-488, $0.76 \mu\text{m}$ [$.000030$] MIN THICKNESS
- 8 NICKEL PLATE PER QQ-N-290, $3.81 \mu\text{m}$ [$.000150$] MIN THICKNESS
- 9 TIN PLATE PER ASTM-B-545, $3.81 \mu\text{m}$ [$.000150$] MIN THICK.
- 10. USE INSTRUCTION SHEET 408-2769



5415633-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - DOCK5 27APR2005	Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK J. HAVENER 27APR2005	NAME					
		APVD J. LIPPERT 27APR2005	JACK, RIGHT ANGLE, 75 OHM, PCB, BNC					
	0 PLC ± -	PRODUCT SPEC	SIZE			CAGE CODE	DRAWING NO	RESTRICTED TO
	1 PLC ± -	108-12078						
	2 PLC ± 0.20 [.008]	APPLICATION SPEC	A2			00779	C-5415633	-
	3 PLC ± -	-						
	4 PLC ± -	WEIGHT	4:1			1	OF 1	REV
	ANGLES ± -	-						
MATERIAL	FINISH		CUSTOMER DRAWING			SCALE		
SEE NOTES	SEE NOTES							