

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

38706-8020

Status:

Active

Overview:

Beau™ Barrier Strips

Description:

8.26mm Pitch Beau™ PCB Terminal Strip, without Mounting Ends, Dual Level Terminal Block, 20 Circuits

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Terminal Blocks

Series

38706

Application

N/A

Component Type

One Piece

Overview

Beau™ Barrier Strips

Product Name

Fixed Mount Barrier

Type

Barrier Strip

UPC

883906405441

Physical

Circuits (Loaded)

20

Circuits (maximum)

20

Color - Resin

Black

Entry Angle

N/A

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polysulfone

Net Weight

45.359/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

3.56mm

PCB Retention

None

PCB Thickness - Recommended

1.57mm

Panel Mount

No

Pitch - Mating Interface

8.26mm

Pitch - Termination Interface

8.26mm

Polarized to Mating Part

N/A

Shrouded

Dual-Barrier

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

160°C

Termination Interface: Style

Through Hole

Wire Size AWG

12, 14, 16, 18, 20, 22

Electrical

Current - Maximum per Contact

20A

Voltage - Maximum

300V

Material Info

Old Part Number

70D20-RC

Reference - Drawing Numbers

Sales Drawing

SD-38706-001




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

38706Series

This document was generated on 10/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION