




© COPYRIGHT 2010 BY INDUSTRIAL FIBER OPTICS, INC.
ALL RIGHTS RESERVED.

LIGHT PIPE PREPARATION/INSTALLATION:



NOTES:

1. ROHS COMPLIANT
2. UL 94V-2 FLAMMABILITY RATING
3. -40°C TO 85°C OPERATING TEMPERATURE
4. SUITABLE FOR LIGHT PIPE WITH Ø2.2mm JACKET AND OPTICAL CORE NO GREATER THAN Ø1.5mm



METRIC


REVISIONS

REV	DESCRIPTION	ECO	DATE	DWN	APVD
A	Initial release		11/12/2008	BB	RD
B	Redrew, fixed diameter of mounting hole	0065	2/9/2010	BB	AR

Panel Thickness

3.0±.1

[.118"±.004]



MOUNTING HOLE

PART IS MADE OF TRANSPARENT POLYCARBONATE.

UNLESS OTHERWISE SPECIFIED DIMENSIONS MILLIMETERS [IN.]		PRODUCT	Light Pipe	INDUSTRIAL FIBER OPTICS TEMPE, AZ 85281	
TOLERANCES		MATERIAL	Polycarbonate	NAME	
0 PLC: ±1	SURFACE 3.2/	FINISH		Lens, Light Pipe to Panel	
1 PLC: ±.25	TEXTURE: ∇	DRAWN BY	B. Bidwell		
2 PLC: ±.127		DATE	2/9/2010		
3 PLC: ±.025		CHECKED BY	A. Reyes		
4 PLC: ±.013		DATE	2/11/2010	SIZE	SCALE
ANGLE: ±1/2°				A	4:1
REMOVE BURRS AND SHARP EDGES FLATNESS .005mm PER mm ALL DIMENSIONS AFTER FINISH		DO NOT SCALE DRAWING		PART NUMBER	REV
				51 0370	B
				Sheet 1 of 1	