





.156" [3.96 mm] Contact Centers, .431" [10.95 mm] Insulator Height, Dip Solder/Eyelet/Right Angle

SPECIFICATIONS


- Accommodates .062" $\pm$.008" [1.57 mm $\pm$ 0.20 mm] PC board
- Molded-in key available
- 3 Amps current rating for one contact energized
(for 5 Amps application, consult factory)
- 30 milli Ohms maximum at rated current
- UL Flammability Rating: 94V-0



READOUT



POLARIZING KEY




TERMINATION TYPE

EYELET ACCEPTS 3-#22 AWG




ALTERNATE EYELET SHAPE

* (RE) .014" [0.36] THICK




(SE) .007" [0.18] THICK
(RE) .014" [0.36] THICK


EYELET (SE OR RE)




NARROW DIP SOLDER (RT, RK, RY)



CARD EXTENDER (RT, RK, RY, SE TERMINATIONS ONLY) REQUIRES -S13 MODIFICATION CODE




WIDE DIP SOLDER (RF, RX, RU, RP)




CENTERED DIP SOLDER (SX, SU) AVAILABLE WITH DUAL OR HALF LOADED READOUT TYPE

(RA) .125" [3.18] FOR ALL POSITIONS
(SA) .270" [6.85] 02 THRU 25 POSITIONS
(SA) .230" [5.84] 28 THRU 36 POSITIONS
(SA) .190" [4.82] 43 POSITIONS
TOLERANCE: (RA) $\pm$.025" [0.64]
(SA) $\pm$.040" [1.00]




RIGHT ANGLE, DIP SOLDER (RA, SA)


MOUNTING STYLE



CLEARANCE HOLE (H)




THREADED INSERT (I)



FLOATING BOBBIN (F)



NO MOUNTING EARS (N)



SIDE MOUNTING (S)

* Beryllium Copper & Beryllium Nickel (H, A, J, F, C & W Material Codes) Only.

.156" [3.96 mm] Contact Centers, .431" [10.95 mm] Insulator Height, Dip Solder/Eyelet/Right Angle



PART NUMBER OPTIONS

MATERIALS (INSULATOR/CONTACT)

E = PBT/Phosphor Bronze (Standard)
 R = PPS/Phosphor Bronze
 G = PA9T/Phosphor Bronze
 H = PBT/Beryllium Copper
 A = PPS/Beryllium Copper
 J = PA9T/Beryllium Copper
 *F = PPS/Spinodal (Overall Gold Plating Only)
 Consult Factory for Special Soldering Guidelines
 *C = PPS/Beryllium Nickel (Overall Gold Plating Only)
 *W = PEEK/Beryllium Nickel (Overall Gold Plating Only)
 *Consult factory for availability.
 Refer to Page 7 for Operating/Processing Temperatures

CONTACT FINISH - RoHS Compliant

All platings are Lead Free and have .000050" Nickel underplate

Contact Surface	Termination
B = .000010" Gold	.000100" Pure Tin, Matte
C = .000030" Gold	.000100" Pure Tin, Matte
G = .000010" Gold	.000005" Gold
Y = .000030" Gold	.000005" Gold
Contact Surface	Overall Plating
S = .000010" Gold	.000010" Gold
M = .000030" Gold	.000010" Gold
E = .000100" Pure Tin, Matte	.000100" Pure Tin, Matte

CONTACT CENTERS

M = .156" [3.96 mm]

NUMBER OF CONTACT POSITIONS

See Chart Below

E B M 43 D RK H - Sxxx

MODIFICATION CODE (Consult Factory)
 OMIT FOR STANDARD

-S13 = Card Extender Accepts .062" [1.57 mm] PCB
 (RT, RK, RY, SE Terminations Only)

MOUNTING STYLE (Opposite Page)

H = .125" [3.18 mm] Clearance Holes
 N = No Mounting
 S = Side Mounting
 I = Threaded Insert
 F = Floating Bobbin


TERMINATION TYPE (Opposite Page)

RA = .125" [3.18 mm] Right Angle Dip Solder
 SA = Long Right Angle Dip Solder
 RT = .140" X .137" [3.56 mm X 3.48 mm] Dip Solder
 RK = .140" X .225" [3.56 mm X 5.72 mm] Dip Solder
 RY = .140" X .425" [3.56 mm X 10.80 mm] Dip Solder
 RX = .200" X .137" [5.08 mm X 3.48 mm] Dip Solder
 RF = .200" X .200" [5.08 mm X 5.08 mm] Dip Solder
 RU = .200" X .225" [5.08 mm X 5.72 mm] Dip Solder
 RP = .200" X .408" [5.08 mm X 10.36 mm] Dip Solder
 SX = .110" [2.79 mm] Centered Dip Solder
 SU = .210" [5.33 mm] Centered Dip Solder
 SE = .007" [0.18 mm] Thick Eyelet
 RE = .014" [0.36 mm] Thick Eyelet

READOUT (Opposite Page)

D = Dual
 D = Dual Row/ Crimp to Center for
 Single Readout (SX, SU Termination Only)
 H = Half Loaded

DIMENSIONS Dimensions in [] are in millimeters, all others are in inches.



Tolerances on non-critical dimensions may vary slightly due to shrinkage differential per insulator material; Consult factory.

POSITIONS/ CONTACTS	INCHES						MILLIMETERS					
	A±.008	B±.008	C±.015	D±.010	E MAX	F+.005/-0.015	A±0.20	B±0.20	C±0.38	D±0.25	E MAX	F+0.13/-0.38
02/04	0.156	0.476	0.596	'N' MOUNTING	1.902	0.325	3.96	12.09	15.14	'N' MOUNTING	48.31	8.26
03/06	0.312	0.632	0.752				7.92	16.05	19.10			
04/08*	0.468	0.788	0.908				11.89	20.02	23.06			
06/12	0.780	1.100	1.220	1.533	2.058	0.438	19.81	27.94	30.99	38.94	52.27	11.13
07/14	0.936	1.256	1.376	1.689	2.214		23.77	31.90	34.95	42.90	56.24	
08/16	1.092	1.412	1.532	1.845	2.526		27.74	35.86	38.91	46.86	64.16	
10/20	1.404	1.724	1.844	2.157	2.682		35.66	43.79	46.84	54.79	83.97	
11/22	1.560	1.880	2.000	2.313	2.838		39.62	47.75	50.80	58.75	95.86	
12/24	1.716	2.036	2.156	2.469	3.306		43.59	51.71	54.76	62.71	111.71	
15/30	2.184	2.504	2.624	2.937	3.774		55.47	63.60	66.65	74.60	119.63	
18/36	2.652	2.972	3.092	3.405	4.866		67.36	75.49	78.54	86.49	123.60	
22/44	3.276	3.596	3.716	4.029	5.334		83.21	91.34	94.39	102.34	135.48	
24/48	3.588	3.908	4.028	4.341	5.782		91.14	99.26	102.31	110.26	167.18	
25/50	3.744	4.064	4.184	4.497	6.764	0.500	95.10	103.23	106.27	114.22	194.92	12.70
28/56	4.212	4.532	4.652	4.965	7.461		106.98	115.11	118.16	126.11	198.88	
36/72	5.460	5.780	5.900	6.213			138.68	146.81	149.86	157.81		
43/86	6.552	6.872	6.992	7.305			166.42	174.55	177.60	185.55		
44/88	6.708	7.028	7.148	7.461			170.38	178.51	181.56	189.51		

* Consult factory for availability.