












| REV. | DATE     | DESCRIPTION           |
|------|----------|-----------------------|
| A    | 06/08/04 | UPDATE DRAWING FORMAT |



RECOMMENDED MOUNTING HOLE



- NOTE:
1. CRIMPED FERRULE  
HEX CRIMP SIZE : .128"
  2. CONTACT PIN TO SOLDER
  3. MAX. PANEL THICKNESS = 6.4mm

| NO. | DESCRIPTION    | MATERIAL     | FINISH  | QTY | DO NOT SCALE DRAWING   | APPROVALS                  | DATE   | PART DESCRIPTION |        |          |
|-----|----------------|--------------|---------|-----|--|----------------------------|--|------------------|--------|----------|
| 1   | HEX NUT        | BRASS        | NICKEL  | 1   | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.<br>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 - 8mm ± 0.20mm<br>8 - 30mm ± 0.40mm<br>30 - 120mm ± 0.50mm<br>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 - .315 = ± 0.007"<br>.315 - 1.180 = ± 0.015"<br>1.180 - 4.724 = ± 0.020" | DRAWN G.R.S.<br>06/08/04   | N FRONT BULKHEAD CRIMP JACK<br>(FOR RG-174/U, 188A/U, 316/U) |                  |        |          |
| 2   | LOCK WASHER    | BRASS        | NICKEL  | 1   |  |                            |  |                  |        |          |
| 3   | GASKET         | SILICONE     | RED     | 1   |  |                            |  |                  |        |          |
| 4   | FERRULE        | COPPER       | NICKEL  | 1   |  |                            |  |                  |        |          |
| 5   | HEX NUT        | BRASS        | NICKEL  | 1   |  |                            |  |                  |        |          |
| 6   | INSULATOR      | TEFLON       | NATURAL | 1   |  |                            |  |                  |        |          |
| 7   | CONTACT PIN    | PHOS. BRONZE | GOLD    | 1   |  |                            |  |                  |        |          |
| 8   | INSULATOR BODY | TEFLON       | NATURAL | 1   |  |                            |  |                  |        |          |
| 1   | DESCRIPTION    | MATERIAL     | FINISH  | QTY | DO NOT SCALE DRAWING   | CAD FILE C:/172/172221.DWG | DWG. NO. 172221.DWG  | REV. A           | SIZE A | SCALE NA |

**Amphenol Connex**