

High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

General Description

The MAX2032 high-linearity passive upconverter or downconverter mixer is designed to provide +33dBm IIP3, 7dB NF, and 7dB conversion loss for a 650MHz to 1000MHz RF frequency range to support a multitude of base-station applications. With a 650MHz to 1250MHz LO frequency range, this particular mixer is ideal for high-side LO injection architectures. For a pin-to-pin-compatible mixer meant for low-side LO injection, refer to the MAX2029.

In addition to offering excellent linearity and noise performance, the MAX2032 also yields a high level of component integration. This device includes a double-balanced passive mixer core, a dual-input LO selectable switch, and an LO buffer. On-chip baluns are also integrated to allow for a single-ended RF input for downconversion (or RF output for upconversion) and single-ended LO inputs. The MAX2032 requires a nominal LO drive of 0dBm, and supply current is guaranteed to be below 100mA.

The MAX2032 is pin compatible with the MAX2039/MAX2041 1700MHz to 2200MHz mixers, making this family of passive upconverters and downconverters ideal for applications where a common PCB layout is used for both frequency bands.

The MAX2032 is available in a compact 20-pin thin QFN package (5mm x 5mm) with an exposed pad. Electrical performance is guaranteed over the extended -40°C to +85°C temperature range.

Applications

WCDMA/LTE and cdma2000® Base Stations

GSM 850/GSM 900 2G and 2.5G EDGE Base Stations

Integrated Digital Enhanced Network (iDEN®) Base Stations

WiMAX™ Base Stations and Customer Premise Equipment

Predistortion Receivers

Microwave and Fixed Broadband Wireless Access

Wireless Local Loop

Digital and Spread-Spectrum Communication Systems

cdma2000 is a registered trademark of Telecommunications Industry Association.

iDEN is a registered trademark of Motorola, Inc.

WiMAX is a trademark of WiMAX Forum.

MAX2032

Features

- ◆ 650MHz to 1000MHz RF Frequency Range
- ◆ 650MHz to 1250MHz LO Frequency Range
- ◆ 570MHz to 900MHz LO Frequency Range (Refer to the MAX2029 Data Sheet)
- ◆ DC to 250MHz IF Frequency Range
- ◆ 7dB Conversion Loss
- ◆ +33dBm Input IP3
- ◆ +24dBm Input 1dB Compression Point
- ◆ 7dB Noise Figure
- ◆ Integrated LO Buffer
- ◆ Integrated RF and LO Baluns
- ◆ Low -3dBm to +3dBm LO Drive
- ◆ Built-In SPDT LO Switch with 49dB LO1 to LO2 Isolation and 50ns Switching Time
- ◆ Pin Compatible with the MAX2039/MAX2041 1700MHz to 2200MHz Mixers
- ◆ External Current-Setting Resistor Provides Option for Operating Mixer in Reduced-Power/Reduced-Performance Mode

Ordering Information


| PART | TEMP RANGE | PIN-PACKAGE |
|--------------|----------------|-----------------|
| MAX2032ETP+ | -40°C to +85°C | 20 Thin QFN-EP* |
| MAX2032ETP+T | -40°C to +85°C | 20 Thin QFN-EP* |

*Denotes a lead(Pb)-free/RoHS-compliant package.

T = Tape and reel.

*EP = Exposed pad.

Pin Configuration/ Functional Diagram



High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

ABSOLUTE MAXIMUM RATINGS

| | |
|--|-----------------------------|
| V_{CC} to GND | -0.3V to +5.5V |
| RF (RF is DC shorted to GND through a balun) | 50mA |
| LO1, LO2 to GND | -0.3V to +0.3V |
| IF+, IF- to GND | -0.3V to (V_{CC} + 0.3V) |
| TAP to GND | -0.3V to +1.4V |
| LOSEL to GND | -0.3V to (V_{CC} + 0.3V) |
| LOBIAS to GND | -0.3V to (V_{CC} + 0.3V) |
| RF, LO1, LO2 Input Power (Note 1) | +20dBm |

| | |
|---------------------------------------|--|
| Continuous Power Dissipation (Note 2) | 5W |
| θ_{JA} (Notes 3, 4) | +38°C/W |
| θ_{JC} (Notes 2, 3) | +13°C/W |
| Operating Temperature Range (Note 5) | $T_C = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |
| Junction Temperature | +150°C |
| Storage Temperature Range | -65°C to +150°C |
| Lead Temperature (soldering, 10s) | +300°C |

Note 1: Maximum, reliable, continuous input power applied to the RF and IF port of this device is +12dBm from a 50Ω source.

Note 2: Based on junction temperature $T_J = T_C + (\theta_{JC} \times V_{CC} \times I_{CC})$. This formula can be used when the temperature of the exposed pad is known while the device is soldered down to a PCB. See the *Applications Information* section for details. The junction temperature must not exceed +150°C.

Note 3: Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to www.maxim-ic.com/thermal-tutorial.

Note 4: Junction temperature $T_J = T_A + (\theta_{JA} \times V_{CC} \times I_{CC})$. This formula can be used when the ambient temperature of the PCB is known. The junction temperature must not exceed +150°C.

Note 5: T_C is the temperature on the exposed pad of the package. T_A is the ambient temperature of the device and PCB.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

(Typical Application Circuit, $V_{CC} = 4.75\text{V}$ to 5.25V , no RF signals applied, $T_C = -40^\circ\text{C}$ to $+85^\circ\text{C}$. IF+ and IF- are DC grounded through an IF balun. Typical values are at $V_{CC} = 5\text{V}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|------------------------|----------|------------|------|------|------|-------|
| Supply Voltage | V_{CC} | | 4.75 | 5.00 | 5.25 | V |
| Supply Current | I_{CC} | | | 85 | 100 | mA |
| LOSEL Input Logic-Low | V_{IL} | | | | 0.8 | V |
| LOSEL Input Logic-High | V_{IH} | | | 2 | | V |

RECOMMENDED AC OPERATING CONDITIONS

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|----------------|----------|---|-----|------|-----|-------|
| RF Frequency | f_{RF} | Components tuned for the 700MHz band (Table 1), $C_1 = 7\text{pF}$, $C_5 = 3.3\text{pF}$ (Notes 6, 7) | 650 | 850 | | MHz |
| | | Components tuned for the 800MHz/900MHz cellular band (Table 1), $C_1 = 82\text{pF}$, $C_5 = 2.0\text{pF}$ (Note 6) | 800 | 1000 | | |
| LO Frequency | f_{LO} | (Notes 6, 7) | 650 | 1250 | | MHz |
| IF Frequency | f_{IF} | IF frequency range depends on external IF transformer selection | 0 | 250 | | MHz |
| LO Drive Level | P_{LO} | (Note 6) | -3 | +3 | | dBm |

High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

AC ELECTRICAL CHARACTERISTICS (800MHz/900MHz CELLULAR BAND DOWNCONVERTER OPERATION)

(Typical Application Circuit, optimized for the **800MHz/900MHz cellular band** (see **Table 1**), $C_1 = 82\text{pF}$, $C_5 = 2\text{pF}$, L_1 and C_4 not used, $V_{CC} = 4.75\text{V}$ to 5.25V , RF and LO ports driven from 50Ω sources, $P_{LO} = -3\text{dBm}$ to $+3\text{dBm}$, $PRF = 0\text{dBm}$, $f_{RF} = 815\text{MHz}$ to 1000MHz , $f_{LO} = 960\text{MHz}$ to 1180MHz , $f_{IF} = 160\text{MHz}$, $f_{LO} > f_{RF}$, $T_C = -40^\circ\text{C}$ to $+85^\circ\text{C}$, unless otherwise noted. Typical values are at $V_{CC} = 5\text{V}$, $PRF = 0\text{dBm}$, $P_{LO} = 0\text{dBm}$, $f_{RF} = 910\text{MHz}$, $f_{LO} = 1070\text{MHz}$, $f_{IF} = 160\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.) (Note 8)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|--|------------------|---|-----|------------|-----|-------|
| Conversion Loss | L_C | | | 7.0 | | dB |
| Conversion Loss Flatness | | Flatness over any one of three frequency bands ($f_{IF} = 160\text{MHz}$): $f_{RF} = 827\text{MHz}$ to 849MHz $f_{RF} = 869\text{MHz}$ to 894MHz $f_{RF} = 880\text{MHz}$ to 915MHz | | ± 0.18 | | dB |
| Conversion Loss Variation Over Temperature | | $T_C = +25^\circ\text{C}$ to -40°C | | -0.3 | | dB |
| | | $T_C = +25^\circ\text{C}$ to $+85^\circ\text{C}$ | | 0.2 | | |
| Input 1dB Compression Point | $P_{1\text{dB}}$ | (Note 9) | | 24 | | dBm |
| Input Third-Order Intercept Point | IIP_3 | $f_{RF1} = 910\text{MHz}$, $f_{RF2} = 911\text{MHz}$, $PRF = 0\text{dBm/tone}$, $f_{LO} = 1070\text{MHz}$, $P_{LO} = 0\text{dBm}$, $T_C = +25^\circ\text{C}$ (Note 10) | 29 | 33 | | dBm |
| Input IP3 Variation Over Temperature | IIP_3 | $T_C = +25^\circ\text{C}$ to -40°C | | 0.3 | | dB |
| | | $T_C = +25^\circ\text{C}$ to $+85^\circ\text{C}$ | | -0.3 | | |
| 2LO - 2RF Spurious Response at IF | 2×2 | | | 65 | | dBc |
| 3LO - 3RF Spurious Response at IF | 3×3 | | | 75 | | dBc |
| Noise Figure | NF | Single sideband | | 7.0 | | dB |
| Noise Figure Under Blocking (Note 11) | | $P_{BLOCKER} = +8\text{dBm}$ | | 18 | | dB |
| | | $P_{BLOCKER} = +12\text{dBm}$ | | 22 | | |
| LO1-to-LO2 Isolation (Note 10) | | LO_2 selected, $P_{LO} = +3\text{dBm}$, $T_C = +25^\circ\text{C}$ | 42 | 51 | | dB |
| | | LO_1 selected, $P_{LO} = +3\text{dBm}$, $T_C = +25^\circ\text{C}$ | 42 | 49 | | |
| Maximum LO Leakage at RF Port | P_{LO} | $= +3\text{dBm}$ | | -27 | | dBm |
| Maximum LO Leakage at IF Port | P_{LO} | $= +3\text{dBm}$ | | -35 | | dBm |
| LO Switching Time | | 50% of LOSEL to IF, settled within 2 degrees | | 50 | | ns |
| Minimum RF-to-IF Isolation | | | | 45 | | dB |
| RF Port Return Loss | | | | 17 | | dB |
| LO Port Return Loss | | LO_1/LO_2 port selected, LO_2/LO_1 , RF, and IF terminated into 50Ω | | 28 | | dB |
| | | LO_1/LO_2 port unselected, LO_2/LO_1 , RF, and IF terminated into 50Ω | | 30 | | |
| IF Port Return Loss | | LO driven at 0dBm , RF terminated into 50Ω | | 17 | | dB |

High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

AC ELECTRICAL CHARACTERISTICS (700MHz BAND DOWNCONVERTER OPERATION)

(Typical Application Circuit, optimized for the **700MHz band** (see Table 1), C1 = 7pF, C5 = 3.3pF, L1 and C4 are not used, V_{CC} = 4.75V to 5.25V, RF and LO ports driven from 50Ω sources, P_{LO} = -3dBm to +3dBm, P_{RF} = 0dBm, f_{RF} = 650MHz to 850MHz, f_{LO} = 790MHz to 990MHz, f_{IF} = 140MHz, f_{LO} > f_{RF}, T_C = +25°C, unless otherwise noted. Typical values are at V_{CC} = 5V, P_{RF} = 0dBm, P_{LO} = 0dBm, f_{RF} = 750MHz, f_{LO} = 890MHz, f_{IF} = 140MHz, T_C = +25°C, unless otherwise noted.) (Notes 8, 10)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|-----------------------------------|------------------|---|-----|-----|-----|-------|
| Conversion Loss | L _C | | 6.1 | 6.9 | 8.1 | dB |
| Input 1dB Compression Point | P _{1dB} | f _{RF} = 750MHz, P _{RF} = 0dBm, P _{LO} = 0dBm | | 24 | | dBm |
| Input Third-Order Intercept Point | IIP3 | f _{RF1} = 749MHz, f _{RF2} = 750MHz, f _{LO} = 890MHz, P _{RF} = 0dBm/tone, P _{LO} = 0dBm | 29 | 33 | | dBm |
| LO Leakage at IF Port | | P _{LO} = +3dBm | | -33 | | dBm |
| LO Leakage at RF Port | | P _{LO} = +3dBm | | -20 | | dBm |
| RF-to-IF Isolation | | | 36 | 49 | | dB |
| 2LO - 2RF Spurious Response | 2 × 2 | | | 65 | | dBc |
| 3LO - 3RF Spurious Response | 3 × 3 | | | 75 | | dBc |

AC ELECTRICAL CHARACTERISTICS (UPCONVERTER OPERATION)

(Typical Application Circuit, L1 = 4.7nH, C4 = 6pF, C1 = 82pF, C5 not used, V_{CC} = 4.75V to 5.25V, RF and LO ports are driven from 50Ω sources, P_{LO} = -3dBm to +3dBm, P_{IF} = 0dBm, f_{RF} = 815MHz to 1000MHz, f_{LO} = 960MHz to 1180MHz, f_{IF} = 160MHz, f_{LO} > f_{RF}, T_C = -40°C to +85°C, unless otherwise noted. Typical values are at V_{CC} = 5V, P_{IF} = 0dBm, P_{LO} = 0dBm, f_{RF} = 910MHz, f_{LO} = 1070MHz, f_{IF} = 160MHz, T_C = +25°C, unless otherwise noted.) (Note 8)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|--|------------------|--|------|------|-----|--------|
| Conversion Loss | L _C | | | 7.4 | | dB |
| Conversion Loss Flatness | | Flatness over any one of three frequency bands (f _{IF} = 160MHz): f _{RF} = 827MHz to 849MHz f _{RF} = 869MHz to 894MHz f _{RF} = 880MHz to 915MHz | | ±0.3 | | dB |
| Conversion Loss Variation Over Temperature | | T _C = +25°C to -40°C | -0.3 | | | dB |
| | | T _C = +25°C to +85°C | 0.4 | | | |
| Input 1dB Compression Point | P _{1dB} | (Note 9) | | 24 | | dBm |
| Input Third-Order Intercept Point | IIP3 | f _{IF1} = 160MHz, f _{IF2} = 161MHz, P _{IF} = 0dBm/tone, f _{LO} = 1070MHz, P _{LO} = 0dBm, T _C = +25°C (Note 10) | 28 | 31 | | dBm |
| Input IP3 Variation Over Temperature | IIP3 | T _C = +25°C to -40°C | 1.2 | | | dB |
| | | T _C = +25°C to +85°C | -0.9 | | | |
| LO ± 2IF Spur | | | 64 | | | dBc |
| LO ± 3IF Spur | | | 83 | | | dBc |
| Output Noise Floor | | P _{OUT} = 0dBm (Note 11) | | -167 | | dBm/Hz |

Note 6: Operation outside this range is possible, but with degraded performance of some parameters.

Note 7: Not production tested.

Note 8: All limits include external component losses. Output measurements are taken at IF or RF port of the *Typical Application Circuit*.

Note 9: Compression point characterized. It is advisable not to continuously operate the mixer RF/IF inputs above +12dBm.

Note 10: Guaranteed by design.

Note 11: Measured with external LO source noise filtered, so its noise floor is -174dBm/Hz. This specification reflects the effects of all SNR degradations in the mixer, including the LO noise as defined in Application Note 2021: *Specifications and Measurement of Local Oscillator Noise in Integrated Circuit Base Station Mixers*.










High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics

(Typical Application Circuit, optimized for the 800MHz/900MHz cellular band (see Table 1), $C_1 = 82\text{pF}$, $C_5 = 2\text{pF}$, L_1 and C_4 not used, $V_{CC} = 5.0\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 160\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

Downconverter Curves

MAX2032












High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 800MHz/900MHz cellular band (see Table 1), $C_1 = 82\text{pF}$, $C_5 = 2\text{pF}$, L_1 and C_4 not used, $V_{CC} = 5.0\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 160\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

Downconverter Curves












High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

MAX2032

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 800MHz/900MHz cellular band (see Table 1), $C_1 = 82\text{pF}$, $C_5 = 2\text{pF}$, L_1 and C_4 not used, $V_{CC} = 5.0\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 160\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

Downconverter Curves












High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 800MHz/900MHz cellular band (see Table 1), $C_1 = 82\text{pF}$, $C_5 = 2\text{pF}$, L_1 and C_4 not used, $V_{CC} = 5.0\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 160\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

Downconverter Curves












High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)
 (Typical Application Circuit, optimized for the 700MHz band (see Table 1), $C_1 = 7\text{pF}$, $C_5 = 3.3\text{pF}$, L_1 and C_4 are not used, $V_{CC} = 5\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 140\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

MAX2032

Downconverter Curves












High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 700MHz band (see Table 1), $C_1 = 7\text{pF}$, $C_5 = 3.3\text{pF}$, L_1 and C_4 are not used, $V_{CC} = 5\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 140\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)


Downconverter Curves











High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 700MHz band (see Table 1), $C_1 = 7\text{pF}$, $C_5 = 3.3\text{pF}$, L_1 and C_4 are not used, $V_{CC} = 5\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 140\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)



Downconverter Curves








High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, optimized for the 700MHz band (see Table 1), $C_1 = 7\text{pF}$, $C_5 = 3.3\text{pF}$, L_1 and C_4 are not used, $V_{CC} = 5\text{V}$, $P_{LO} = 0\text{dBm}$, $P_{RF} = 0\text{dBm}$, $f_{LO} > f_{RF}$, $f_{IF} = 140\text{MHz}$, $T_C = +25^\circ\text{C}$, unless otherwise noted.)

Downconverter Curves












High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, L1 = 4.7nH, C4 = 6pF, C5 not used, V_{CC} = 5.0V, P_{LO} = 0dBm, P_{IF} = 0dBm, f_{RF} = f_{LO} + f_{IF}, f_{IF} = 160MHz, T_C = +25°C, unless otherwise noted.)










Upconverter Curves



High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)

(Typical Application Circuit, L1 = 4.7nH, C4 = 6pF, C5 not used, V_{CC} = 5.0V, P_{LO} = 0dBm, P_{IF} = 0dBm, f_{RF} = f_{LO} + f_{IF}, f_{IF} = 160MHz, T_C = +25°C, unless otherwise noted.)




High-Linearity, 650MHz to 1000MHz Upconversion/ Downconversion Mixer with LO Buffer/Switch

Typical Operating Characteristics (continued)


(Typical Application Circuit, L1 = 4.7nH, C4 = 6pF, C5 not used, V_{CC} = 5.0V, P_{LO} = 0dBm, P_{IF} = 0dBm, f_{RF} = f_{LO} + f_{IF}, f_{IF} = 160MHz, T_C = +25°C, unless otherwise noted.)

Upconverter Curves


LO LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)




LO LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)




LO LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)




IF LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)




IF LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)



IF LEAKAGE AT RF PORT vs. LO FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)



RF PORT RETURN LOSS vs. RF FREQUENCY
(L-C BPF TUNED FOR 810MHz RF FREQUENCY)



High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Pin Description

| PIN | NAME | FUNCTION |
|------------------------------|----------|--|
| 1, 6, 8, 14 | VCC | Power-Supply Connection. Bypass each VCC pin to GND with capacitors as shown in the <i>Typical Application Circuit</i> . |
| 2 | RF | Single-Ended 50Ω RF Input/Output. This port is internally matched and DC shorted to GND through a balun. |
| 3 | TAP | Center Tap of the Internal RF Balun. Connect to ground. |
| 4, 5, 10, 12, 13, 16, 17, 20 | GND | Ground |
| 7 | LOBIAS | Bias Resistor for Internal LO Buffer. Connect a 523Ω ±1% resistor from LOBIAS to the power supply. |
| 9 | LOSEL | Local Oscillator Select. Logic-control input for selecting LO1 or LO2. |
| 11 | LO1 | Local Oscillator Input 1. Drive LOSEL low to select LO1. |
| 15 | LO2 | Local Oscillator Input 2. Drive LOSEL high to select LO2. |
| 18, 19 | IF-, IF+ | Differential IF Input/Outputs |
| — | EP | Exposed Pad. Internally connected to GND. Solder this exposed pad to a PCB pad that uses multiple ground vias to provide heat transfer out of the device into the PCB ground planes. These multiple ground vias are also required to achieve the noted RF performance. |

Detailed Description

The MAX2032 can operate either as a downconverter or an upconverter mixer that provides approximately 7dB of conversion loss with a typical 7dB noise figure. IIP3 is +33dBm and +31dBm for downconversion and upconversion modes, respectively. The integrated baluns and matching circuitry allow for 50Ω single-ended interfaces to the RF port and the two LO ports. The RF port can be used as an input for downconversion or an output for upconversion. A single-pole, double-throw (SPDT) switch provides 50ns switching time between the two LO inputs with 49dB of LO-to-LO isolation. Furthermore, the integrated LO buffer provides a high drive level to the mixer core, reducing the LO drive required at the MAX2032's inputs to a -3dBm to +3dBm range. The IF port incorporates a differential output for downconversion, which is ideal for providing enhanced IIP2 performance. For upconversion, the IF port is a differential input.

Specifications are guaranteed over broad frequency ranges to allow for use in cellular band WCDMA, cdmaOne™, cdma2000, and GSM 850/GSM 900 2.5G EDGE base stations. The MAX2032 is specified to operate over a 650MHz to 1000MHz RF frequency range, a 650MHz to 1250MHz LO frequency range, and a DC to 250MHz IF frequency range. Operation beyond these ranges is possible; see the *Typical Operating Characteristics* for additional details.

The MAX2032 is optimized for high-side LO injection architectures. However, the device can operate in low-side LO

injection applications with an extended LO range, but performance degrades as f_{LO} decreases. See the *Typical Operating Characteristics* for measurements taken with f_{LO} below 960MHz. For a pin-compatible device that has been optimized for LO frequencies below 960MHz, refer to the MAX2029.

RF Port and Balun

For using the MAX2032 as a downconverter, the RF input is internally matched to 50Ω, requiring no external matching components. A DC-blocking capacitor is required because the input is internally DC shorted to ground through the on-chip balun. For upconverter operation, the RF port is a single-ended output similarly matched to 50Ω.

LO Inputs, Buffer, and Balun

The MAX2032 is optimized for high-side LO injection architectures with a 650MHz to 1250MHz LO frequency range. For a device with a 570MHz to 900MHz LO frequency range, refer to the MAX2029. As an added feature, the MAX2032 includes an internal LO SPDT switch that can be used for frequency-hopping applications. The switch selects one of the two single-ended LO ports, allowing the external oscillator to settle on a particular frequency before it is switched in. LO switching time is typically less than 50ns, which is more than adequate for nearly all GSM applications. If frequency hopping is not employed, set the switch to either of the LO inputs. The switch is controlled by a digital input (LOSEL): logic-high selects LO2, logic-low selects LO1.

cdmaOne is a trademark of CDMA Development Group.

High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

To avoid damage to the part, voltage **MUST** be applied to VCC before digital logic is applied to LOSEL (see the *Absolute Maximum Ratings*). LO1 and LO2 inputs are internally matched to 50Ω , requiring an 82pF DC-blocking capacitor at each input.

A two-stage internal LO buffer allows a wide input-power range for the LO drive. All guaranteed specifications are for a -3dBm to +3dBm LO signal power. The on-chip low-loss balun, along with an LO buffer, drives the double-balanced mixer. All interfacing and matching components from the LO inputs to the IF outputs are integrated on-chip.

High-Linearity Mixer

The core of the MAX2032 is a double-balanced, high-performance passive mixer. Exceptional linearity is provided by the large LO swing from the on-chip LO buffer.

Differential IF

The MAX2032 mixer has a DC to 250MHz IF frequency range. Note that these differential ports are ideal for providing enhanced IIP2 performance. Single-ended IF applications require a 1:1 balun to transform the 50Ω differential IF impedance to 50Ω single-ended. Including the balun, the IF return loss is better than 15dB. The differential IF is used as an input port for upconverter operation. The user can use a differential IF amplifier following the mixer, but a DC block is required on both IF pins.

Table 1. Typical Application Circuit Component List

| DESIGNATION | QTY | DESCRIPTION | SUPPLIER |
|---------------------------|-----|---|--|
| C1 | 1 | 82pF microwave capacitor (0603). Use for 800MHz/900MHz cellular band applications. | Murata Electronics North America, Inc. |
| | | 7pF microwave capacitor (0603). Use for 700MHz band applications. | |
| C2, C7, C8, C10, C11, C12 | 6 | 82pF microwave capacitors (0603) | Murata Electronics North America, Inc. |
| C3, C6, C9 | 3 | 0.01 μ F microwave capacitors (0603) | Murata Electronics North America, Inc. |
| C4* | 1 | 6pF microwave capacitor (0603) | — |
| C5** | 1 | 2pF microwave capacitor (0603). Use for 800MHz/900MHz cellular band applications. | Murata Electronics North America, Inc. |
| | | 3.3pF microwave capacitor (0603). Use for 700MHz band applications. | |
| L1* | 1 | 4.7nH inductor (0603) | — |
| R1 | 1 | 523 Ω $\pm 1\%$ resistor (0603) | Digi-Key Corp. |
| T1 | 1 | MABAES0029 1:1 transformer (50:50) | M/A-Com, Inc. |
| U1 | 1 | MAX2032 IC (20 TQFN) | Maxim Integrated Products, Inc. |

*C4 and L1 installed only when mixer is used as an upconverter.

**C5 installed only when mixer is used as a downconverter.

Applications Information

Input and Output Matching

The RF and LO inputs are internally matched to 50Ω . No matching components are required. As a downconverter, the return loss at the RF port is typically better than 15dB over the entire input range (650MHz to 1000MHz), and return loss at the LO ports are typically 15dB (960MHz to 1180MHz). RF and LO inputs require only DC-blocking capacitors for interfacing (see Table 1).

An optional L-C bandpass filter (BPF) can be installed at the RF port to improve upconverter performance. See the *Typical Application Circuit* and *Typical Operating Characteristics* for upconverter operation with an L-C BPF tuned for 810MHz RF frequency. Performance can be optimized at other frequencies by choosing different values for L1 and C4. Removing L1 and C4 altogether results in a broader match, but performance degrades. Contact factory for details.

The IF output impedance is 50Ω (differential). For evaluation, an external low-loss 1:1 (impedance ratio) balun transforms this impedance to a 50Ω single-ended output (see the *Typical Application Circuit*).

High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Bias Resistor

Bias current for the LO buffer is optimized by fine tuning resistor R1. If reduced current is required at the expense of performance, contact the factory for details. If the $\pm 1\%$ bias resistor values are not readily available, substitute standard $\pm 5\%$ values.

Layout Considerations

A properly designed PCB is an essential part of any RF/microwave circuit. Keep RF signal lines as short as possible to reduce losses, radiation, and inductance. For the best performance, route the ground-pin traces directly to the exposed pad under the package. The PCB exposed pad **MUST** be connected to the ground plane of the PCB. It is suggested that multiple vias be used to connect this pad to the lower-level ground planes. This method provides a good RF/thermal conduction path for the device. Solder the exposed pad on the bottom of the device package to the PCB. The MAX2032 evaluation kit can be used as a reference for board layout. Gerber files are available upon request at www.maxim-ic.com.

Power-Supply Bypassing


Proper voltage-supply bypassing is essential for high-frequency circuit stability. Bypass each V_{CC} pin with the capacitors shown in the *Typical Application Circuit*. See Table 1.

Exposed Pad RF/Thermal Considerations

The exposed pad (EP) of the MAX2032's 20-pin thin QFN-EP package provides a low-thermal-resistance path to the die. It is important that the PCB on which the MAX2032 is mounted be designed to conduct heat from the EP. In addition, provide the EP with a low-inductance path to electrical ground. The EP **MUST** be soldered to a ground plane on the PCB, either directly or through an array of plated via holes.

High-Linearity, 650MHz to 1000MHz Upconversion/Downconversion Mixer with LO Buffer/Switch

Typical Application Circuit



Chip Information

PROCESS: SiGe BiCMOS

Package Information

For the latest package outline information and land patterns, go to www.maxim-ic.com/packages. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

| PACKAGE TYPE | PACKAGE CODE | DOCUMENT NO. |
|----------------|--------------|----------------|
| 20 Thin QFN-EP | T2055+3 | 21-0140 |

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600

19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Maxim Integrated:](#)

[MAX2032ETP+](#) [MAX2032ETP+T](#)