



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family SLIM LINE			
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM scale 4:1	title				
E	V61462	MDF	10/14/96	angles linear	.XXX±.01/.XXX±.03				PRESS FIT HEADER ASS'Y SLIM LINE 4 WALL				
F	V61785	SAR	12/13/96		.XXX±.005/.XXX±.013								
G	V61745	MDF	1/23/97		.XXX±.0020/.XXX±.0051								
H	V20526	RGD	3/18/02										
J	M05-0099	MHT	5/24/05	enrg	M. CLUSER	8/27/87		dwg no		sheet 1 of 5		size	
K	M07-0116	AGS	2/24/07	chr	R. DOUTRICH	10/6/88		68712		A3			
L	M07-0489	MHT	11/13/07	appd	R. DOUTRICH	10/6/88		type		Product Customer Drawing			
sheet index	revision sheet	L	L	L	L	L							
		1	2	3	4	5							

1

2 3

4

5




6

PRODUCT NUMBER

SEE TABLE



NOTES:

- ① MOLDING MATERIAL: 30% GLASS FILLED POLYESTER
FLAME RETARDENT PER UL94V-O. COLOR-BLUE.
- ② TERMINAL MATERIAL: PHOSPHOR BRONZE.
- ③ REFER TO TA 556 FOR APPLICATION, TOOLING
AND INSTRUCTIONS.
4. UNLESS OTHERWISE SPECIFIED, 1° MAX DRAFT
PERMISSIBLE ON ALL SURFACES.
5. LOGO LOCATION OPTIONAL.
- ⑥ TWO NON-CRITICAL SIDES OF PIN TIP NOT
PLATED TYP BOTH ENDS.
7. 3 LBS / .36 KG PIN RETENTION IN BOTH
DIRECTIONS.
8. RECOMMENDED PLATED-THRU-HOLE DIMENSIONS ARE:
DRILLED HOLE: .0453/1.151±.0010/.025 DIA
COPPER PLATING THICKNESS: .001/.025 TO .003/.076
SOLDER PLATING THICKNESS: .0003/.076 TO .0007/.0178
OVERALL HOLE SIZE: .040/1.016±.003/.076 DIA
- ⑨ ON HEADERS 2 X 20 AND LARGER THE .260/6.6 DIM
HAS A MINIMUM SIZE OF .240/6.1.
- ⑩ PIN PLATING-DUPLEX- 30u"/.076u Au OVER 50u"/1.27uNi
ON CONTACT AREA OF PIN AND 40u"/1.02u-80u"/2.03u
TIN/LEAD ON PRESS FIT AREA OF PIN.
LEAD FREE: PIN PLATING-DUPLEX- 30u"/.076u Au OVER 50u"/1.27uNi
ON CONTACT AREA OF PIN AND 40u"/1.02u-80u"/2.03u
PURE TIN ON PRESS FIT AREA OF PIN.
- ⑪ PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE.
12. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑬ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
14. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING
SOLDER PROCESS.

2 X 5
STYLE A2 X 7
STYLE C2 X 5
STYLE B2 X 8 & LARGER
STYLE D

FCIconnect.com

Copyright FCI

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family SLIM LINE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title			
L					angles	linear	$XX \pm .01 / XX \pm 0.3$					PRESS FIT HEADER ASS'Y SLIM LINE 4 WALL			
					$0' \pm 2'$		$XXX \pm .005 / XXX \pm 0.13$								
							$XXXX \pm .0020 / XXX \pm 0.051$								
					dr	M. CLUSER	8/27/87			dwg no		sheet 2 of 5		size	
				enrg	B. TROSTLE	8/27/87	68712			A3					
				chr	R. DOUTRICH	10/6/88									
				appd	R. DOUTRICH	10/6/88									
sheet index		revision sheet													

form: A3

1

2

3

4

5

6



FCIconnect.com

Copyright FCI

D

PRODUCT NUMBER	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 13	STYLE
68712-025LF	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-026LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-027LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-028LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-029LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-030LF	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-031LF	2 X 13	1.58/40.13	1.52/38.61	1.200/30.48	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-032LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-033LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-034LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-035LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-036LF	2 X 13	1.58/40.13	1.52/38.61	1.200/30.48	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-037LF	2 X 15	1.78/45.21	1.72/43.69	1.400/35.56	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-038LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-039LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-040LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-041LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-042LF	2 X 15	1.78/45.21	1.72/43.69	1.400/35.56	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-043LF	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-044LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-045LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-046LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-047LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
68712-048LF	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D

mat'l. code				surface ISO 1302 <input checked="" type="checkbox"/>		tolerance ISO 406 ISO 1101		projection 		product family SLIM LINE			
ltr				ecn no		dr		date		title			
L										PRESS FIT HEADER ASS'Y			
				angles		linear		INCH/MM		SLIM LINE 4 WALL			
				0°±2'				scale 4:1		dwg no			
										sheet 4 of 5 size			
										68712 A3			
										type Product Customer Drawing			
sheet index		revision sheet											

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 13	STYLE
68712-049LF	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-050LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-051LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-052LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-053LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-054LF	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-055LF	2 X 22	2.48/62.99	2.42/61.47	2.100/53.34	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-056LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-057LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-058LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-059LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-060LF	2 X 22	2.48/62.99	2.42/61.47	2.100/53.34	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-061LF	2 X 25	2.78/70.61	2.72/69.09	2.400/60.96	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-062LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-063LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-064LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-065LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-066LF	2 X 25	2.78/70.61	2.72/69.09	2.400/60.96	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-067LF	2 X 30	3.28/83.31	3.22/81.79	2.900/73.66	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-068LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-069LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-070LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-071LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-072LF	2 X 30	3.28/83.31	3.22/81.79	2.900/73.66	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	
-073LF	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.160/4.06	50u"/1.27u Au OVER 50u"/1.27u Ni	D
-074LF	2 X 5	.78/19.81	.72/18.29	.400/10.16	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	A
-075LF	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-076LF	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	D
68712-201LF	2 X 5	.78/19.81	.72/18.29	.400/10.16	.160/4.06	SEE NOTE 10	A
68712-201	2 X 5	.78/19.81	.72/18.29	.400/10.16	.160/4.06	SEE NOTE 10	A
68712-219LF	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.160/4.06	SEE NOTE 10	D
68712-219	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.160/4.06	SEE NOTE 10	D

mat'l. code				surface ISO 1302 <input checked="" type="checkbox"/>		tolerance ISO 406 ISO 1101		projection 		product family SLIM LINE			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
L								angles linear 0°±2'		XX±.01/XX±0.3 XXXX±.005/XXX±0.13 XXXX±.0020/XXX±0.051		INCH/MM scale 4:1	
								dr M. CLUSER 8/27/87 engr B. TROSTLE 8/27/87 chr R. DOUTRICH 10/6/88 appd R. DOUTRICH 10/6/88				title PRESS FIT HEADER ASS'Y SLIM LINE 4 WALL	
										dwg no 68712		sheet 5 of 5 size A3	
sheet index		revision sheet								type Product Customer Drawing			

form: A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[68712-038](#) [68712-050](#) [68712-013](#)