






Part No. & Date code Printing




ORDERING INFORMATION

SERIES	D B P V 25 P 0 64 C T X XXX LF	LEAD FREE
SHELL SIZE	E,A,B,C,D	APPLICABLE ONLY FOR DP SERIES
CHARACTERISATION	M-DM SERIES P-DP SERIES	SPECIAL CODE
OPTIONS	BLANK-STANDARD F-FLOAT MOUNTING (Only for DM) L-CLINCH NUT (M3) O-CLINCH NUT (UNC) V-FEM. SCREW LOCK HEX. (UNC) (Only for DP) N-THR FEM. SCREW LOCK M3	DIMPLES - OPTIONAL X-ON MALE DP CONNECTORS ONLY
NO.OF CONTACTS	09,15,25,37,50	SHELL PLATING
CONTACTS	P - PIN S - SOCKET	BLANK-ZINC for DP/CADMIUM for DM T-STD (Only for DP). TIN over Cu or Zinc Cr 3
TERMINATION TYPE	0-SOLDER BUCKET	OPTIONS
		BLANK-STANDARD H-SHIELDING TERMINATION FINGERS (Only for DP) N- OBLIGATORY FOR DM
		CONTACT PLATING
		DP SERIES ONLY 64 - 200 MATING CYCLES 65 - 500 MATING CYCLES
		32 - 1.27µ Au (Code 32 APPLICABLE FOR DM SERIES ONLY)

"This LF product meets European Union Directives and other country regulations as described in GS-22-008"


Packaging as per GS-14-920

WITH SHIELDING TERMINATION FINGERS




OPTION: H


MALE LEVER LOCK

ORD CODE 8630-3427(EABC)
,, 8630-3428(D)

FEMALE LEVER LOCK


ORD CODE 8630-3425(EABC)
,, 8630-3426(D)

FEMALE SCREW LOCK



8630-01	M3	M3
8630-01A	M3	4-40 UNC 2
8630-01B	4-40 UNC 2A	4-40 UNC 2B
ORD-CODE	EXTERNAL THREAD	INTERNAL THREAD

FEMALE SCREW LOCK EXTEND TYPE



ORD CODE 8630-01-061

TECHNICAL SPECIFICATIONS

SHELLS	: TIN/CADMIUM/ZINC PLATED STEEL
INSULATOR MATERIAL	: SELF EXTINGUISHING THERMOPLASTIC- TO UL CLASS 94 V0
	HOUSING WILL WITHSTAND EXPOSURE TO 260-265°C IF USE PROTECTIVE ADHESIVE (type Kapton or Teflon) OR PROTECTIVE METALLIC DEVICE
CONTACT DIA ON ACTIVE AREA:	Ø1 MM.
CONTACTS MATERIAL	: COPPER ALLOY
CONTACT PLATING	: GXT / GOLD OVER NICKEL
OPERATING TEMPERATURE	: -55°C +125°C
OPERATING CURRENT	: 7.5 A PER CONTACT
CONTACT RESISTANCE	: ≤7.3 mΩ
INSULATION RESISTANCE	: ≥5000 MΩ
MAXIMUM VOLTAGE	: 1000 V.r.m.s
MECHANICAL ENDURANCE	: 500 MATINGS FOR CODE 65 : 200 MATINGS FOR CODE 64
DAMP HEAT	: 56 DAYS FOR CODE 65 : 21 DAYS FOR CODE 64

mat'l. code	surface	tolerance	projection	product family
SEE NOTE 4	ISO 1302 ✓	ISO 406 ISO 1101	MM	D-SUB
ltr	ecn no	dr	date	title
G	i06-074	GVJ	2006-06-08	D-SUB S/B CONNECTOR
H	I08-0047	MRA	2008-03-25	(DP & DM SERIES WITH ASSEMBLY OPTIONS)
J	I09-0078	MRA	2009-05-15	
K	I09-0111	MRA	2009-06-23	
L	I09-0288	MRA	2009-12-23	
M	I11-0003	MRA	2011-01-06	
sheet	revision	M		dwg no
index	sheet	1		sheet 1 of 1
				size
				A3
				type
				Product Customer Drawing