




COIL: @ +25 °C

RESISTANCE 440 OHMS ± 10%

NOMINAL VOLTAGE 11.0-23 VDC

MUST OPERATE 6.65 VDC

MUST RELEASE 4.0 VDC MAX 0.66 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX

RELEASE 5 MS MAX

CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/22/92 CK 12/22/92

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. GENICOM
CUST. NO. 3SAV5004F2

TYPE "HMS" RELAY

HMS1201S48