

## Rear panel feed-through - RC-0000000Q0FZ - 1592924

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Rear panel feed-through, series: RC, straight, Axial O-ring, Central fixing, shielded: yes

RoHS

IP67

### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 193443 |
| GTIN                                 | 4046356193443                                                                                           |
| Weight per Piece (excluding packing) | 105.250 g                                                                                               |
| Custom tariff number                 | 85366990                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### General

|               |                                                                                           |
|---------------|-------------------------------------------------------------------------------------------|
| Note          | Order information: Order contact inserts and cable clamping/shield accessories separately |
| Mounting type | Central fixing                                                                            |

#### Ambient conditions

|                      |                   |
|----------------------|-------------------|
| Ambient temperature  | -20 °C ... 125 °C |
| Degree of protection | IP67              |

#### Material

|                            |                                                                      |
|----------------------------|----------------------------------------------------------------------|
| Housing material           | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Gasket and O-ring material | FPM                                                                  |

Specifications according to DIN EN 61984:2001

## Rear panel feed-through - RC-0000000Q0FZ - 1592924

### Technical data

Specifications according to DIN EN 61984:2001


|                          |        |
|--------------------------|--------|
| Installation height max. | 2000 m |
|--------------------------|--------|

### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |


### Drawings

Diagram




## Rear panel feed-through - RC-0000000Q0FZ - 1592924

Diagram




Dimensional drawing



## Rear panel feed-through - RC-0000000Q0FZ - 1592924

Dimensional drawing



### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440312 |
| eCl@ss 4.0    | 27260700 |
| eCl@ss 4.1    | 27260700 |
| eCl@ss 5.0    | 27260700 |
| eCl@ss 5.1    | 27260700 |
| eCl@ss 6.0    | 27260700 |
| eCl@ss 7.0    | 27440312 |
| eCl@ss 8.0    | 27440312 |
| eCl@ss 9.0    | 27440312 |

## Rear panel feed-through - RC-0000000Q0FZ - 1592924

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC001121 |
| ETIM 5.0 | EC002641 |
| ETIM 6.0 | EC002641 |
| ETIM 7.0 | EC002641 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11     | 43172015 |
| UNSPSC 12.01  | 43201404 |
| UNSPSC 13.2   | 39121419 |
| UNSPSC 18.0   | 39121419 |
| UNSPSC 19.0   | 39121419 |
| UNSPSC 20.0   | 39121419 |
| UNSPSC 21.0   | 39121419 |

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

#### Approval details

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01687 |
|-----|-------------------------------------------------------------------------------------|---------|