






PART NO.
20021121



- NOTES:
1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION INFRA-RED OR VAPOR PHASE REFLOW OVEN.
3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4.PRODUCT SPEC: GS-12-629
5.PACKAGE SPEC: GS-14-1420
6.04~38 PDS: 0.1mm
40~100 PDS: 0.14mm



PRODUCT WITH CAP



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®					
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title UNSHROUDED HDR VT SMT							
L	ELX-N-23548	TIM	03/21/16	angles linear		.0±.30			dwg no sheet 1 of 2 size A3						
M	ELX-N-23949	TIM	04/26/16			.00±.20									
N	ELX-N-28817	TONY	12/18/17			.000±.10									
				dr	ZK HU	8/1/12			type Product Customer Drawing						
				engr	ZK HU	8/1/12			20021121						
				chr	BIAN RICK	8/1/12									
				appd	BIAN RICK	8/1/12									
sheet index		revision sheet		N	N										
				1	2										

