


## SPECIFICATIONS PT-2300


Typical values for batteries stored at 20°C for one year

Nominal Capacity (At 5mA/20°C/68°F/2.0V Cut-Off)	19 Ah
Open Circuit Voltage (At 20°C/68°F)	3.67 V
Nominal Voltage (At 5mA/20°C/68°F)	3.6 V
Maximum Continuous Current	230 mA
Maximum Pulse Current Capability	500 mA
Rated 1 Sec. Pulse Capability (To 3V)	100 mA
Operating Temperature Range	-55° to +85°C (-67° to +185°F)
Weight	97 g (3.26 oz)
Anode Surface Area	40 cm <sup>2</sup> (6.20 in <sup>2</sup> )
Volume	51 cm <sup>3</sup> (7.91 in <sup>3</sup> )
Diameter (Max)	33.6 mm (1.32 in)
Height (Max)	60 mm (2.36 in)


## PRODUCT SCHEMATIC




## DISCHARGE CHARACTERISTICS AT +20°C (68°F)



## CAPACITY vs. CURRENT



## TEMPERATURE vs. OPERATING VOLTAGE



WARNING: Fire, Explosion And Severe Burn Hazard. Do Not Recharge, Crush, Disassemble, Heat Above 212°F (100°C), Incinerate Or Expose Contents To Water

## THE ECONOMICAL HIGH-POWER SOLUTION

The EaglePicher PT Series of KEEPER® cells was developed as an economical, high-power option for design experts who prefer the cylindrical design. With sizes and capacities ranging from the 1200 mAh (PT-2150) to the 19,000 mAh (PT-2300H), this cylindrical design will provide the long life power needed for commercial applications.


## PT SERIES PRODUCT FEATURES

- Compliant with lead-free RoHS and WEEE EC directives.
- Stainless steel construction provides corrosion resistance, hermetic seal and structural integrity.
- Years of low-rate continuous use.
- Stand-by use with 80% capacity retention after 15 years at room temperature.
- Wave solderable  
(limit solder bath exposure to a maximum of 5 seconds).
- High energy density compared to other chemistries.
- No charging circuits required.
- Higher cell voltage allows for fewer cells and high reliability.
- Flat discharge characteristics provide optimum voltage regulation.
- Non-pressurized system allows for high-temperature usage.
- Underwriters Laboratories recognized component.

## WE CAN DESIGN TO FIT ANY APPLICATION.

Our team of engineers can design any pin configuration required to fit your specialized application. If you don't see a battery configuration you need here, call us and we will begin working on a EP part number just for you.

## PT-2300 TERMINAL TYPES



The specifications on this sheet may be changed by EaglePicher without notice.  
EaglePicher™ is a trademark of and Keeper® is a registered trademark of EaglePicher Corporation.

DISTRIBUTED LOCALLY BY:

EaglePicher™ Commercial Power Solutions

Keeper®

3220 Industrial Drive • Joplin, MO 64801

Tel: 1-800-201-0215 • Fax: 417-626-2078

E-mail: [solutions@eaglepicher.com](mailto:solutions@eaglepicher.com) • Web site: [www.epcompower.com](http://www.epcompower.com)

Copyright ©2006 EaglePicher Corporation

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle-Picher:

[PT-2300](#) [PT-2300H-T](#)