

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MAY ,1994.

© COPYRIGHT 1994 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD






C1

REVISED ECO-09-024717

09NOV09

KK

AEG



OBSOLETE

1 MATERIAL & FINISH
CAP HOUSING:THERMOPLASTIC(UL94-V0)
COLOR:BLACK.

POST CONTACT:COPPER ALLOY.
FINISH:OVER NICKEL,MATING END:
0.2μm OR 0.76μm MIN.GOLD,
TERMINATION END:TIN. AND SEALING TREATMENT
ALL OVER.

2 P.W.B. LAYOUT AND P.W.B. TREATMENT(REF.).
P.W.B. SURFACE ARE TREATED WITH SOLDER RESIST.
BOARD THICKNESS:1.6mm.


3 ON KINK POINT(4 PLACES).

4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

鉛フリー
LEAD FREE

GENERAL TOLERANCE
一般公差
10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差MATERIAL
材料FINISH
仕上DWN
T.KAWAMAE

09MAY94

CHK
Y.FUJIURA

09MAY94

APVD
Y.FUJIURA

09MAY94

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

SCALE
尺度 2:1SHEET
1 OF 1REV
C1

Au PL. 0.76[μm] MIN.	20	11	11.43	15.80	17.40	19.20	9	20	46-	-5
	60	31	36.83	41.20	42.80	44.60	29	60	46-	-4
	50	26	30.48	34.85	36.45	38.26	24	50	46-	-3
	40	21	24.13	28.50	30.10	31.90	19	40	46-	-2
	30	16	17.78	22.15	23.75	25.55	14	30	46-	-1
Au PL. 0.2[μm] MIN.	20	11	11.43	15.80	17.40	19.20	9	20	46-	-5
	60	31	36.83	41.20	42.80	44.60	29	60	46-	-4
	50	26	30.48	34.85	36.45	38.26	24	50	46-	-3
	40	21	24.13	28.50	30.10	31.90	19	40	46-	-2
	30	16	17.78	22.15	23.75	25.55	14	30	175711-1	
REMARK	N	M	A	B	C	D	n	POS.	PART NO.	

CIRCUIT NO. DIMENSION

NAME

Tyco Electronics AMP K.K.

Kawasaki,Japan

CAP ASSY V WITH KINK

AMPLIMITE .050 SERIES I B-TO-B CONN.

SIZE

CAGE CODE

DRAWING NO

A3 00779 C-175711

RESTRICTED TO