




	7	6	5	4	3	2	1																																																																																																																																										
E	NOTE:1. OVERMOLD SPECIFICATION: 1.1 DVI BOOT MOLDED WITH SNOW WHITE PVC RESIN P/N IS 887800076. 1.2 UL94V-0, COLOR: MAD432 1.3 HARDNESS (DUROMETER): SHORE A 90-95 1.4 DFP BOOT MOLDED WITH UL94V-0 ABS. 2. MECHANICAL SPECIFICATION: 2.1 CABLE SHOULD STAND THE PULL FORCE 89-111N FOR 30 SECONDS WITH NO VISIBLE TERMINATION DAMAGE.				2.2 CABLE SHOULD PASS THE FLEX TEST IN 100 CYCLES AT EACH OF PLANES, PER EIA 364-41, CONDITION 1. 3. DVI CONNECTOR SPECIFICATION: 3.1 REFER TO PRODUCT SPEC. PS74320-001 3.2 CONTACT PLATING: AU FLASH. 4. THE CODE PLEASE BE PRINTED ON THE SPACE 5. SHORTCIRCUIT AMONG DRAIN WIRES IS ACCEPTABLE 6. THIS PRODUCT MUST MEET MX RoHS COMPLIANCE.				E																																																																																																																																								
D	PINOUTS:								D																																																																																																																																								
C	<table><tr><td>SHIELD</td><td>SHIELD</td><td>BRAID</td><td>GROUND</td></tr><tr><td>PIN 24</td><td>PIN 6</td><td>WHITE</td><td>TMDS CLOCK-</td></tr><tr><td>PIN 23</td><td>PIN 5</td><td>BROWN</td><td>TMDS CLOCK+</td></tr><tr><td>PIN 22</td><td>PIN 4</td><td>BRAID</td><td>TMDS CLOCK SHIELD</td></tr><tr><td>PIN 19</td><td>PIN 14</td><td>BRAID</td><td>TMDS DATA 0 SHIELD</td></tr><tr><td>PIN 18</td><td>PIN 15</td><td>BLUE</td><td>TMDS DATA 0+</td></tr><tr><td>PIN 17</td><td>PIN 16</td><td>WHITE</td><td>TMDS DATA 0-</td></tr><tr><td>PIN 16</td><td>PIN 18</td><td>WHITE</td><td>HOT PLUG DETECT</td></tr><tr><td>PIN 15</td><td>PIN 7</td><td>ORANGE</td><td>GROUND(+5V & HV SYNC.)</td></tr><tr><td>PIN 14</td><td>PIN 8</td><td>YELLOW</td><td>POWER +5V</td></tr><tr><td>PIN 11</td><td>PIN 3</td><td>BRAID</td><td>TMDS DATA 1 SHIELD</td></tr><tr><td>PIN 10</td><td>PIN 1</td><td>GREEN</td><td>TMDS DATA 1+</td></tr><tr><td>PIN 9</td><td>PIN 2</td><td>WHITE</td><td>TMDS DATA 1-</td></tr><tr><td>PIN 7</td><td>PIN 19</td><td>RED</td><td>DDC DATA</td></tr><tr><td>PIN 6</td><td>PIN 20</td><td>VOILET</td><td>DDC CLOCK</td></tr><tr><td>PIN 3</td><td>PIN 13</td><td>BRAID</td><td>TMDS DATA 2 SHIELD</td></tr><tr><td>PIN 2</td><td>PIN 11</td><td>RED</td><td>TMDS DATA 2+</td></tr><tr><td>PIN 1</td><td>PIN 12</td><td>WHITE</td><td>TMDS DATA 2-</td></tr><tr><td>DVI_D</td><td>DFP</td><td>COLOR</td><td>CABLE FUNCTION</td></tr></table>				SHIELD	SHIELD	BRAID	GROUND	PIN 24	PIN 6	WHITE	TMDS CLOCK-	PIN 23	PIN 5	BROWN	TMDS CLOCK+	PIN 22	PIN 4	BRAID	TMDS CLOCK SHIELD	PIN 19	PIN 14	BRAID	TMDS DATA 0 SHIELD	PIN 18	PIN 15	BLUE	TMDS DATA 0+	PIN 17	PIN 16	WHITE	TMDS DATA 0-	PIN 16	PIN 18	WHITE	HOT PLUG DETECT	PIN 15	PIN 7	ORANGE	GROUND(+5V & HV SYNC.)	PIN 14	PIN 8	YELLOW	POWER +5V	PIN 11	PIN 3	BRAID	TMDS DATA 1 SHIELD	PIN 10	PIN 1	GREEN	TMDS DATA 1+	PIN 9	PIN 2	WHITE	TMDS DATA 1-	PIN 7	PIN 19	RED	DDC DATA	PIN 6	PIN 20	VOILET	DDC CLOCK	PIN 3	PIN 13	BRAID	TMDS DATA 2 SHIELD	PIN 2	PIN 11	RED	TMDS DATA 2+	PIN 1	PIN 12	WHITE	TMDS DATA 2-	DVI_D	DFP	COLOR	CABLE FUNCTION	<table><tr><td>N</td><td>UL-TAPE 887804785</td><td>55(Ref.)</td><td>1</td></tr><tr><td>M</td><td>DVI THUMB SCREW 887806077</td><td></td><td>2</td></tr><tr><td>L</td><td>PCB 887899569/887899570</td><td></td><td>2</td></tr><tr><td>K</td><td>DVI METAL CAN 887899392</td><td></td><td>1</td></tr><tr><td>J</td><td>DVI_D SINGLE CHANNEL G/F CONNECTOR 743230101</td><td></td><td>1</td></tr><tr><td>I</td><td>DVI DIGITAL SINGLE LINK CABLE 887808276</td><td>4572(Ref.)</td><td>1</td></tr><tr><td>H</td><td>BEIGE LATCH 887809070</td><td></td><td>2</td></tr><tr><td>G</td><td>COPPER FOIL 887801082</td><td></td><td>1</td></tr><tr><td>F</td><td>LOW INNER MET HOOD 887809072</td><td></td><td>1</td></tr><tr><td>E</td><td>TOP INNER MET HOOD 887809071</td><td></td><td>1</td></tr><tr><td>D</td><td>WIRE COVER 887911256</td><td></td><td>1</td></tr><tr><td>C</td><td>WIRE HOLDER 887911257</td><td></td><td>2</td></tr><tr><td>B</td><td>ABS HOOD 887911255</td><td></td><td>1</td></tr><tr><td>A</td><td>MDR 20 CONNECTOR(ACON) 887899280</td><td></td><td>1</td></tr><tr><td>ITEM</td><td>DESCRIPTION</td><td>L</td><td>QTY.</td></tr></table>				N	UL-TAPE 887804785	55(Ref.)	1	M	DVI THUMB SCREW 887806077		2	L	PCB 887899569/887899570		2	K	DVI METAL CAN 887899392		1	J	DVI_D SINGLE CHANNEL G/F CONNECTOR 743230101		1	I	DVI DIGITAL SINGLE LINK CABLE 887808276	4572(Ref.)	1	H	BEIGE LATCH 887809070		2	G	COPPER FOIL 887801082		1	F	LOW INNER MET HOOD 887809072		1	E	TOP INNER MET HOOD 887809071		1	D	WIRE COVER 887911256		1	C	WIRE HOLDER 887911257		2	B	ABS HOOD 887911255		1	A	MDR 20 CONNECTOR(ACON) 887899280		1	ITEM	DESCRIPTION	L	QTY.	C
SHIELD	SHIELD	BRAID	GROUND																																																																																																																																														
PIN 24	PIN 6	WHITE	TMDS CLOCK-																																																																																																																																														
PIN 23	PIN 5	BROWN	TMDS CLOCK+																																																																																																																																														
PIN 22	PIN 4	BRAID	TMDS CLOCK SHIELD																																																																																																																																														
PIN 19	PIN 14	BRAID	TMDS DATA 0 SHIELD																																																																																																																																														
PIN 18	PIN 15	BLUE	TMDS DATA 0+																																																																																																																																														
PIN 17	PIN 16	WHITE	TMDS DATA 0-																																																																																																																																														
PIN 16	PIN 18	WHITE	HOT PLUG DETECT																																																																																																																																														
PIN 15	PIN 7	ORANGE	GROUND(+5V & HV SYNC.)																																																																																																																																														
PIN 14	PIN 8	YELLOW	POWER +5V																																																																																																																																														
PIN 11	PIN 3	BRAID	TMDS DATA 1 SHIELD																																																																																																																																														
PIN 10	PIN 1	GREEN	TMDS DATA 1+																																																																																																																																														
PIN 9	PIN 2	WHITE	TMDS DATA 1-																																																																																																																																														
PIN 7	PIN 19	RED	DDC DATA																																																																																																																																														
PIN 6	PIN 20	VOILET	DDC CLOCK																																																																																																																																														
PIN 3	PIN 13	BRAID	TMDS DATA 2 SHIELD																																																																																																																																														
PIN 2	PIN 11	RED	TMDS DATA 2+																																																																																																																																														
PIN 1	PIN 12	WHITE	TMDS DATA 2-																																																																																																																																														
DVI_D	DFP	COLOR	CABLE FUNCTION																																																																																																																																														
N	UL-TAPE 887804785	55(Ref.)	1																																																																																																																																														
M	DVI THUMB SCREW 887806077		2																																																																																																																																														
L	PCB 887899569/887899570		2																																																																																																																																														
K	DVI METAL CAN 887899392		1																																																																																																																																														
J	DVI_D SINGLE CHANNEL G/F CONNECTOR 743230101		1																																																																																																																																														
I	DVI DIGITAL SINGLE LINK CABLE 887808276	4572(Ref.)	1																																																																																																																																														
H	BEIGE LATCH 887809070		2																																																																																																																																														
G	COPPER FOIL 887801082		1																																																																																																																																														
F	LOW INNER MET HOOD 887809072		1																																																																																																																																														
E	TOP INNER MET HOOD 887809071		1																																																																																																																																														
D	WIRE COVER 887911256		1																																																																																																																																														
C	WIRE HOLDER 887911257		2																																																																																																																																														
B	ABS HOOD 887911255		1																																																																																																																																														
A	MDR 20 CONNECTOR(ACON) 887899280		1																																																																																																																																														
ITEM	DESCRIPTION	L	QTY.																																																																																																																																														
B								B																																																																																																																																									
A	<table><tr><td rowspan="4">EC NO: DG2006-0096 DRWN:PDAI CHKD: APPR:TKAN A</td><td rowspan="4">2005/10/19 2005/10/19 2005/10/20</td><td rowspan="4">DESCRIPTION</td><td rowspan="4">QUALITY SYMBOLS =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td>DIMENSION STYLE MM/IN</td><td>SCALE ---</td><td>DESIGN UNITS METRIC</td><td rowspan="4">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY PDAI</td><td>DATE 2005/10/19</td><td rowspan="3">TITLE DVI-D(M) TO DFP(M) L=15FT BLACK</td></tr><tr><td>4 PLACES</td><td>±---</td><td>±---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>3 PLACES</td><td>±---</td><td>±---</td><td>PDAI</td><td>2005/10/19</td></tr><tr><td></td><td></td><td></td><td></td><td>2 PLACES</td><td>±---</td><td>±---</td><td>APPROVED BY ZXDENG</td><td>DATE 2005/10/19</td><td rowspan="2">MOLEX INCORPORATED</td></tr><tr><td></td><td></td><td></td><td></td><td>1 PLACE</td><td>±---</td><td>±---</td><td>MATERIAL NO. 68802-0020</td><td>DOCUMENT NO. SD-68802-020</td><td>SHEET NO. 2 OF 2</td></tr><tr><td colspan="4"></td><td colspan="2">ANGULAR ±---°</td><td colspan="4"></td><td></td></tr><tr><td colspan="4"></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="4"></td><td></td></tr><tr><td colspan="4"></td><td colspan="2"></td><td>SIZE A4</td><td colspan="4">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>							EC NO: DG2006-0096 DRWN:PDAI CHKD: APPR:TKAN A	2005/10/19 2005/10/19 2005/10/20	DESCRIPTION	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN	SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		mm	INCH	DRAWN BY PDAI	DATE 2005/10/19	TITLE DVI-D(M) TO DFP(M) L=15FT BLACK	4 PLACES	±---	±---	CHECKED BY	DATE	3 PLACES	±---	±---	PDAI	2005/10/19					2 PLACES	±---	±---	APPROVED BY ZXDENG	DATE 2005/10/19	MOLEX INCORPORATED					1 PLACE	±---	±---	MATERIAL NO. 68802-0020	DOCUMENT NO. SD-68802-020	SHEET NO. 2 OF 2					ANGULAR ±---°											DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				A																																																										
EC NO: DG2006-0096 DRWN:PDAI CHKD: APPR:TKAN A	2005/10/19 2005/10/19 2005/10/20	DESCRIPTION	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN	SCALE ---					DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																				
					mm	INCH	DRAWN BY PDAI					DATE 2005/10/19		TITLE DVI-D(M) TO DFP(M) L=15FT BLACK																																																																																																																																			
				4 PLACES	±---	±---	CHECKED BY					DATE																																																																																																																																					
				3 PLACES	±---	±---	PDAI	2005/10/19																																																																																																																																									
				2 PLACES	±---	±---	APPROVED BY ZXDENG	DATE 2005/10/19	MOLEX INCORPORATED																																																																																																																																								
				1 PLACE	±---	±---	MATERIAL NO. 68802-0020	DOCUMENT NO. SD-68802-020		SHEET NO. 2 OF 2																																																																																																																																							
				ANGULAR ±---°																																																																																																																																													
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																																																																																													
						SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																										
	tb_frame_A4_P_ME_T Rev. D 2004/04/02	6	5	4	3	2	1																																																																																																																																										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[68802-0020](#)