




EVERLIGHT ELECTRONICS CO., LTD.

Device Number: DPT-092-090 REV: 1.0
MODEL NO: PT928-6B ECN: Page: 1/7

Package Dimensions:



Office: NO 25, Lane.76, Chung Yang Rd., Sec.3, Tucheng, Taipei 236, Taiwan, R.O.C.

TEL: 886-2-2267-2000, 2267-9936 (22 Lines)

FAX: 886-2-2267-6189

http: [//www.everlight.com](http://www.everlight.com)



EVERLIGHT ELECTRONICS CO., LTD.

Device Number: DPT-092-090 REV: 1.0
MODEL NO: PT928-6B ECN: Page: 2/7

©Notes :

- 1.All dimensions are in millimeter.
- 2.Lead spacing is measured where the lead emerge from the package .
- 3.Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 4.These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
- 5.When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

Description

The **PT928-6B** is a high speed and high sensitivity single photo transistor;molded in a black plastic package with spherical side view lens.

The device is spectrally matched with IR emitters.

Features

- Wide angle of half sensitivity $\theta = \pm 25^\circ$
- High sensitivity
- Fast response time

Applications

- Mouse
- Optoelectronic Switch
- Photo Interrupter



EVERLIGHT ELECTRONICS CO., LTD.

Device Number: DPT-092-090REV: 1.0MODEL NO: PT928-6BECN: Page: 3/7**Absolute Maximum Ratings**

(Ta=25°C)

ITEM	SYMBOL	RATING	UNIT
Collector Power Dissipation	P _c	75	mW
Collector-Emitter Voltage	V _{CEO}	30	V
Emitter-Collector Voltage	V _{ECO}	5	V
Collector Current	I _c	20	mA
Operating Temperature	T _{opr}	-25~+85	°C
Storage Temperature	T _{stg}	-40~+85	°C
Soldering Temperature (1/16 inch from body for 5 seconds)	T _{sol}	260	°C

Electro-Optical Characteristics

(Ta=25°C)

Parameter		Symbol	Min	Typ	Max	Unit	Condition
Collector Dark Current		I _{CEO}	-	-	100	nA	V _{CE} =20V, Ee=0mW/cm ²
C-E Saturation Voltage		V _{CE(Sat)}	-	-	0.4	V	I _c =0.5mA, Ee=10mW/cm ²
Light Current		I _L	0.6	-	4.0	mA	V _{CE} =5V, I _F =5mA
The Wavelength of Peak Sensitivity		λ _p	-	860	-	nm	---
Range of Spectral Bandwidth		λ _{0.5}		700...1200	-	nm	---
Response Time	Rise Time	t _r	-	15	-	μ Sec	V _{CE} =5V I _c =1mA R _L =1000 Ω
	Fall Time	t _f	-	15	-	μ Sec	
Half sensitivity angle		Δ θ	-	± 25	-	°	---



Device Number: DPT-092-090 REV: 1.0
MODEL NO: PT928-6B ECN: Page: 4/7

Typical Characteristics

Fig.1 Collector Power Dissipation vs. Ambient Temperature




Fig.2 Collector Dark Current vs. Ambient Temperature




Fig. 3 Relative Collector Current vs. Ambient Temperature




Fig.4 Collector Current vs. Irradiance




Fig.5 Spectral Sensitivity






Fig.6 Collector Current vs. Collector-emitter Voltage





Test Method

The light current testing method for PTR:



Rankings

Parameter	Symbol	Min	Max	Unit	Test Condition
6-1	I _L	2.0	4.0	mA	V _{CE} =5V I _F =5mA
6-2		1.8	3.5		
7-1		1.4	2.6		
7-2		1.0	2.0		
7-3		0.6	1.4		

Supplements

1.Parts

(1) Chip

Type	Material	Peak Wavelength
PT	Silicon	860nm

(2) Material

Type	Lead frame	Wire	Package
Material	SPCC	Gold	Epoxy



Device Number: DPT-092-090 REV: 1.0
MODEL NO: PT928-6B ECN: Page: 6/7

Reliability

The reliability of products shall be satisfied with items listed below.

Confidence level : 90%

LTPD : 10%


Test Items	Test Conditions	Failure Judgement Criteria	Samples(n)
			Defective(c)
Operating life test	$V_{CE}=5V$ $T_a : 25^{\circ}C$ 1000hrs	$I_L \leq L \times 0.8$ $L : \text{Lower specification limit}$	n =22 , c=0
Temperature cycle	1cycle $-55^{\circ}C$ to $+25^{\circ}C$ to $+85^{\circ}C$ (30min) (5min) (30min) 50 cycle test		n =22 , c=0
Thermal shock	$-55^{\circ}C$ to $+85^{\circ}C$ (5min) (5min) 50cycle test		n =22 , c=0
High temperature storage	Temp : $+100^{\circ}C$ 1000hrs		n =22 , c=0
Low temperature storage	Temp : $-55^{\circ}C$ 1000hrs		n =22 , c=0
High temperature High humidity	$T_a : 85^{\circ}C$ RH : 85% 1000hrs		n =22 , c=0
Solder heat	Temp : $260 \pm 5^{\circ}C$ 10 sec		n =22 , c=0
Solderability	Temp : $230 \pm 5^{\circ}C$ 3 sec		n =22 , c=0



EVERLIGHT ELECTRONICS CO., LTD.

Device Number: DPT-092-090 REV: 1.0
MODEL NO: PT928-6B ECN: Page: 7/7

Packing Specifications



CPN: Customer's product number
P/N: Product number
QTY: Packing quantity
CAT: Ranks
HUE: Peak wavelength
REF: Reference
LOT NO: Lot number
MADE IN TAIWAN: Production place

Packing Quantity Specification

- 1.1000Pcs/1bag , 10bags/1box
- 2.10boxes/1Carton