


The C4710 series are PC-board mountable high voltage supplies for photomultiplier tubes. The series has six standard versions.

FEATURES

- Compact and Lightweight
- High Stability
- High Output Power
- Complete Fail-safe Functions
- Six-plane Metal Shielded




TACCF0113

SPECIFICATIONS

Parameter		C4710 Series						Unit
		C4710	C4710-01	C4710-02	C4710-50	C4710-51	C4710-52	
Input Voltage		+15 ± 1	+12 ± 1	+24 ± 1	+15 ± 1	+12 ± 1	+24 ± 1	Vdc
Input Current at Maximum	with no load	95	120	65	95	120	65	mA (Typ.)
Output Voltage	with full load	260	340	145	260	340	145	
Specification Guaranteed Output Voltage Range		-240 to -1500			+240 to +1500			Vdc
Output Current		1						mA (Max.)
Input Regulation against ± 1V Input Change		±0.01	±0.015	±0.015	±0.02	±0.02	±0.015	% (Typ.)
Load Regulation against 0 to 100% Load Change		±0.01	±0.015	±0.01	±0.01	±0.01	±0.01	% (Typ.)
Ripple / Noise (p-p)		0.005						% (Typ.)
Output Voltage Controlling Modes		By external controlling voltage (+0.8 to +5 V) or external potentiometer (10 kΩ)						—
Controlling Voltage Input Impedance		40			56			kΩ (Typ.)
Output Voltage Setting		±(Controlling voltage× 300) ± 0.5%						V
Output Voltage Rise Time (0 →100%)		100						ms (Typ.)
Temperature Coefficient		±0.01						%/°C(Typ.)
Operating Temperature Range		+5 to +40						°C
Storage Temperature Range		-10 to +60						°C
Dimensions (W × H × D)		65 × 27.5 × 45						mm
Weight		105						g
Protective Functions		Units protected against reversed power input, reversed/excessive controlling voltage input, continuous overloading/short circuit in output						—

HIGH VOLTAGE POWER SUPPLY UNIT C4710 SERIES

Figure 1: Output Voltage Controlling



TACCC0052EB

Figure 2: Output Voltage Controlling Characteristics






Figure 3: Example of Ripple / Noise Reduction Circuit



TACCC0053EB

Figure 4: Dimensional outline (Unit: mm)



TACCA0124EA

HAMAMATSU

HAMAMATSU PHOTONICS K.K., Eelectron Tube Center

314-5, Shimokanzo, Toyooka-village, Iwata-gun, Shizuoka-ken, 438-0193, Japan, Telephone: (81)539/62-5248, Fax: (81)539/62-2205

U.S.A.: Hamamatsu Corporation: 360 Foothill Road, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1)908-231-0960, Fax: (1)908-231-1218

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-2658

France: Hamamatsu Photonics France S.A.R.L.: 8, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 00, Fax: (33)1 69 53 71 10

United Kingdom: Hamamatsu Photonics UK Limited: Lough Point, 2 Gladbeck Way, Windmill Hill, Enfield, Middlesex EN2 7JA, United Kingdom, Telephone: (44)181-367-3560, Fax: (44)181-367-6384

North Europe: Hamamatsu Photonics Norden AB: Fäaröagatan 7, S-164-40 Kista Sweden, Telephone: (46)8-703-29-50, Fax: (46)8-750-58-95

Italy: Hamamatsu Photonics Italia: S.R.L.: Via Della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39)2-935 81 733, Fax: (39)2-935 81 741

TACC1003E04
MAR. 1995 E
Printed in Japan