




PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
CBR2S	.160 (4.1)	2.0 (50.8)	.044 (1.1)	.190 (4.8)	.190 (4.8)	.280 (7.1)	.332 (8.4)	7.6 (193)	50 (222)	STANDARD	.24 (107)
CBR3S	.280 (7.1)	3.0 (76.2)	.052 (1.3)	.190 (4.8)	.215 (5.5)	.280 (7.1)	.332 (8.4)	10.8 (274.3)	50 (222)	STANDARD	.39 (174.8)
CBR4S	.280 (7.1)	4.0 (101.6)	.052 (1.3)	.190 (4.8)	.215 (5.5)	.280 (7.1)	.332 (8.4)	14.0 (355.6)	50 (222)	STANDARD	.48 (218.6)
CBR2HS	.160 (4.1)	2.0 (50.8)	.058 (1.4)	.250 (6.4)	.240 (6.1)	.326 (8.2)	.388 (9.9)	8.0 (203.2)	85 (378)	HEAVY/ STANDARD	.43 (195)
CBR4LH	.315 (8.0)	4.0 (101.6)	.070 (1.8)	.300 (7.6)	.322 (8.2)	.400 (10.2)	.490 (12.4)	14.6 (370.8)	120 (534)	LIGHT/ HEAVY	1.13 (515.8)
CBR6LH	.315 (8.0)	6.0 (152.4)	.070 (1.8)	.300 (7.6)	.322 (8.2)	.400 (10.2)	.490 (12.4)	20.9 (530.9)	120 (534)	LIGHT/ HEAVY	1.61 (731.5)

NOTE(S) :

* SEE CURRENT PRICE SHEET TO DETERMINE PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

SS-27295_00

PANDUIT CORP. TINLEY PARK, ILLINOIS

CBR SERIES CABLE TIE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .01(.25) (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE NONE

DATE
6/22/01

NYLON 6/6

DRAWING NO.

SS-27295

DWG
A
SIZE

3 11/18/03 JABO REVISED CBR4/6LH DIM. E TO .490
(12.4), WAS .475(12.1)

27295 3

REV DATE BY CHK DESCRIPTION

ECN - R

CUST

SUP

CHK'D
TGS