

ELEVATED SOCKETS ESW & ESQ SERIES

Mates with:
TSW, MTSW, EW, MTLW,
TSS, ZSS,
TSM, DW, ZW, HW

SPECIFICATIONS

For complete specifications
see www.samtec.com?ESW
or www.samtec.com?ESQ

Insulator Material:
Black Glass Filled
Polyester

Contact Material:
Phosphor Bronze

Plating:
Au or Sn over

50 μ " (1,27 μ m) Ni

Current Rating:
3A continuous

Voltage Rating:
550 VAC mated with

TSW or ESQ

Operating Temp Range:
-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:
10 m Ω max

Insertion Depth:
(3,68mm) .145" to

(6,35mm) .250"

Insertion Force:
(Single contact only)

(-S plating)

Standard = 6oz (1,67N) avg

((0,64mm) .025" SQ pin);

ESW Low Insertion Force=

3oz (0,83N) avg

ESQ Low Insertion Force=

3.3oz (0,92N) avg

Normal Force:
Standard = 125 grams (4,4N)

Withdrawal Force:
(Single contact only)

(-S plating)

Standard = 5oz (1,39N) avg

((0,64mm) .025" SQ pin);

ESW Low Insertion Force=

2.6oz (0,72N) avg

ESQ Low Insertion Force=


2.9oz (0,81N) avg

Max Cycles:
100 with 10 μ " (0,25mm) Au

Lead-Free Solderable:
Wave only



TYPE STRIP	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
ESW = Solder Tail					-S = Single Row	-LL = Locking Lead
ESQ = Square Tail				-G = 20 μ " (0,51 μ m) Gold Contact, Gold Flash on Balance	-D = Double Row	Two leads per strip crimped. N/A with single row 1 or 2 positions.
				-S = 30 μ " (0,76 μ m) Gold on Contact area, Matte Tin on Tail	-T = Triple Row (ESQ only)	
				-T = Matte Tin (N/A w/LIF contact)		
Specify LEAD STYLE from chart below.						



STANDARD INSERTION FORCE	LOW INSERTION FORCE	A	B
- 12	- 37	(2,29) .090	(11,05) .435
- 13	- 38	(7,36) .290	
- 23	- 48	(4,83) .190	(13,59) .535
- 33	- 58	(2,29) .090	(16,13) .635
- 14	- 39	(12,19) .480	(11,05) .435
- 24	- 49	(9,65) .380	(13,59) .535
- 34	- 59	(7,11) .280	(16,13) .635
- 44	- 69	(4,57) .180	(18,67) .735

APPLICATIONS

Self Nesting Sockets
(ESQ Series)

PC/104 J1/P1 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-14-G-D
Low Insertion Force	ESQ-132-39-G-D
PC/104 J1 "Non-Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-12-G-D
Low Insertion Force	ESQ-132-37-G-D
PC/104 J2/P2 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-120-14-G-D
Low Insertion Force	ESQ-120-39-G-D

PC/104 is a trademark of the PC/104 Consortium.

Note: Some lengths,
styles and options are
non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-87420413
SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
SAMTEC JAPAN • Tel: 81-424-42-8318 • Fax: 81-424-42-8319
SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-53854047
SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432
SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187
SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745