

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: PHOSPHOR BRONZE(SIGNAL CONTACT)

BRASS (POWERS CONTACT)

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)

30A (POWER CONTACT)

-CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL and POWER)

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 24 HOURS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m Maximum


- Female screw : 0.5 N.m Maximum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-47-0004.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec:
 - Signal contacts: Ni + Gold/GxT
 - Power contacts: Ni 1.27µm+Sn 2.5 to 7.5µm,pure bright
- Active area plating spec:
 - Signal and power contacts: Ni + Gold/GxT
- Shell plating :2 to 4µm Cu + Ni + 3 to 10µmm Sn,pure bright
- Accessories: Sn pure bright + Nickel
- Packaging spec: See GS-14-920

TABLE 1:PCB HOLE DIAMETERS

POWER CONTACTS			ACCESSORIES	SIGNAL CONTACTS
30 A	2.00	Ø2.40	ø3.10	ø1.00
Max current power	ØA±0.10	PCB HOLE +/-0.1	PCB HOLE +/-0.1	PCB HOLE +/-0.1




spec ref				dr 1, Product Eng		2015/06/12		projection		mm		size A2		scale 1:1			
tolerance std				eng Paul Mithun		2019/02/20						ecn no		ELX-1-32325-2			
ISO 406				chr -		-						rel level		Released			
ISO 1101				appr K-Paul Biju		2019/02/20						product family		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED				Amphenol FCI		title		SUB FEMALE DW US foot print				dwg no		C01-8639-2301C		rev	
surface				linear		0.X ±3		mixed power right angled solder								E	
ISO 1302				angular		0° ±2°		cat. no. -				Product - Customer Drw				sheet 1 of 6	



Amphenol
FCi

© 2016 AFCI

spec ref			dr		1, Product Eng		2015/06/12		projection		mm		size		A2		scale		1:1													
tolerance std			eng		Paul Mithun		2019/02/20						ecn no		ELX-132325-2																	
ISO 406			chr		-		-		product family				-		rel level						Released											
ISO 1101			appr		K-Paul Biju		2019/02/20																									
surface			linear		0.X		±3		Amphenol FCI		title		SUB FEMALE DW US foot print								dwg no		C01-8639-2301C						rev		E	
					0.XX		±0.10						mixed power right angled solder																			
					0.XXX		±±0.05																									
ISO 1302			angular		0°		±2°				cat. no.		-		Product - Customer Drw								sheet 2 of 6									

PDS: Rev :E

STATUS:Released

Printed: Feb 20, 2019

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS700A30LF	30	200	without	without
D*LxWxS700A30LF	30	200	insert M3	without
D*OxWxS700A30LF	30	200	insert UNC 4.40	without
D*VxWxS700A30LF	30	200	female screw UNC 4.40	without
D*xWxS700H30LF	30	200	without	metal bracket+harpoon PCB 2.40mm
D*LxWxS700H30LF	30	200	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxS700H30LF	30	200	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxS700H30LF	30	200	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxS700G30LF	30	200	without	metal bracket+harpoon PCB 1.60mm
D*LxWxS700G30LF	30	200	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxS700G30LF	30	200	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxS700G30LF	30	200	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxS700M30LF	30	200	without	metal bracket
D*LxWxS700M30LF	30	200	insert M3	metal bracket
D*OxWxS700M30LF	30	200	insert UNC 4.40	metal bracket
D*VxWxS700M30LF	30	200	female screw UNC 4.40	metal bracket

shell size * LAYOUTS
xWx

A

A

B

B

B

C

C

C

11W1

7W2

21W1

17W2

13W3

25W3

21WA4





27W2

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS743A30LF	30	500	without	without
D*LxWxS743A30LF	30	500	insert M3	without
D*OxWxS743A30LF	30	500	insert UNC 4.40	without
D*VxWxS743A30LF	30	500	female screw UNC 4.40	without
D*xWxS743H30LF	30	500	without	metal bracket+harpoon PCB 2.40mm
D*LxWxS743H30LF	30	500	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxS743H30LF	30	500	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxS743H30LF	30	500	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxS743G30LF	30	500	without	metal bracket+harpoon PCB 1.60mm
D*LxWxS743G30LF	30	500	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxS743G30LF	30	500	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxS543G30LF	30	500	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxS743M30LF	30	500	without	metal bracket
D*LxWxS743M30LF	30	500	insert M3	metal bracket
D*OxWxS743M30LF	30	500	insert UNC 4.40	metal bracket
D*VxWxS743M30LF	30	500	female screw UNC 4.40	metal bracket

spec ref		dr		1, Product Eng	2015/06/12			size	A2	scale	1:1	
tolerance std		eng		Paul Mithun	2019/02/20			ecn no		rel level	Released	
ISO 406		chr		-	-							
ISO 1101		appr		K-Paul Biju	2019/02/20							product family
TOLERANCES UNLESS OTHERWISE SPECIFIED		Amphenol FCI		title SUB FEMALE DW US foot print mixed power right angled solder		dwg no C01-8639-2301C		rev E				
surface		linear		0.X	±3							
ISO 1302		angular		0°		±2°						





13W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I







21W1

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



17W2


LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



spec ref		dr		1, Product Eng		2015/06/12		projection		mm		size		A2		scale		2:1	
tolerance std		eng		Paul Mithun		2019/02/20						ecn no		ELX-132325-2		rel level		Released	
ISO 406		chr		-		-													
ISO 1101		appr		K-Paul Biju		2019/02/20													
surface		linear		Amphenol FCi		title		SUB FEMALE DW US foot print		dwg no		C01-8639-2301C		rev		E			
		0.X																±3	
		0.XX																±0.10	
						</													


21WA4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I




25W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



27W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



spec ref		dr		1, Product Eng		2015/06/12		projection		mm		size		scale							
tolerance std		eng		Paul Mithun		2019/02/20						A2		2:1							
ISO 406		chr		-		-						ecn no		ELX-32325-2							
ISO 1101		appr		K-Paul Biju		2019/02/20						product family		-		Released					
surface		linear		0.X		±3		Amphenol FCi		title		SUB FEMALE DW US foot print		dwg no		C01-8639-2301C		rev			
ISO 1302				0.XX		±0.10														mixed power right angled solder	
				0.XXX		±±0.05															
		angular		0°		±2°		cat. no.		-		Product - Customer Drw		sheet 6 of 6							