


Electrical Commercial and Industrial

3M™ Cable Tie CT15BK120-D

3M ID 80611469729 UPC# 00051128593134 3M Product Number 59313 3M Product Number CT15BK120-D



3M™ Cable Ties are made with high quality 6/6 nylon and designed to secure wire bundles and harness components quickly, without slipping.

The 3M™ Cable Tie CT15BK120-D is 15.0" in length. UV Weather Resistant Black. 120 lb tensile strength. 500 pcs/bag.

- Plenum Rated
- Self Locking Head
- Curved tip allows for faster threading and installation
- UV weather resistant for outdoor use



[Overview](#) [Documentation](#)

Specifications

Agency Approvals	UL Listed 62275 Type 21
Cable Length	15 Inch
Cable Length (mm)	381 mm
China RoHS - Below MCV	Yes
Color	Black
EU RoHS Compliant	Yes
Flammability Rating	UL 94 V-2
Length	15 Inch
Length (metric)	381 Millimetre
Length Range	14-16 Inch
Material	Nylon 6/6
Maximum Bundle Diameter	4 Inch
Maximum Bundle Diameter (metric)	102 mm
Maximum Operating Temperature (Celsius)	85 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	185 Degree Fahrenheit
Mil Spec	MS3367-3-0
Minimum Bundle Diameter	0.1875 Inch
Minimum Installation Temperature (Celsius)	-20 Degree Celsius
Minimum Installation Temperature (Fahrenheit)	-4 Degree Fahrenheit
Operating Temperature Range (Celsius)	-40 to 85 Degree Celsius

Operating Temperature Range (Fahrenheit)	-40 to 185 Degree Fahrenheit
Plenum Rated	Yes
Tensile Strength	530 N, 54.43109 kg, Light Heavy Duty (110-120 lb)
Thickness	0.069 Inch
Thickness (mm)	1.8 mm
Type	Standard
Units per Bag	500
Units per Case	2500
UV Resistance	Yes
Width	0.298 Inch
Width (mm)	7.6

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.