

PART NAME	PLASTICASE			PART No.	PC-11463, PC-11464 & PC-11465				
-----------	------------	--	--	----------	-------------------------------	--	--	--	--

Front View Dimensions:

- Width: 6.142
- Height: 7.086
- Thickness: 0.090
- Bottom Panel Dimensions: 5.855 (Width), 5.709 (Exposed Panel), H (Panel thickness)
- Side View Dimensions: 0.359 (Bottom), 0.055 TYP. (Bottom), 5.752 (Bottom), 5.862 (Bottom), 6.676 (Bottom), 0.140 TYP. (Bottom), 0.098 TYP. (Bottom), 0.472 (Bottom), 0.216 DIA. BOSS WITH 0.090 DIA. HOLE x 0.156 DEEP (12 PLACES) (Bottom), 0.296 DIA. BOSS (8 PLACES) (Top), 0.472 (Top), 1.732 (Top), 2.348 (Top), 3.543 (Top), 7.086 (Top), 0.359 (Top)
- Section "A-A" View: Shows internal structure with labels A through J.

MATERIAL: ABS THERMOPLASTIC (UL 94-HB RATED)

FINISH: TOP & BOTTOM _____ LIGHT GRAY PANELS _____ DARK GRAY

FOR PC-11463 & PC-11464
FOUR (4) M3 x 1.000 LG SCREWS SUPPLIED
FOR ASSEMBLING BOTTOM TO TOP.

FOR PC-11465
FOUR (4) M3 x 1.218 LG SCREWS SUPPLIED
FOR ASSEMBLING BOTTOM TO TOP.

FOUR (4) RUBBER STICK-ON FEET SUPPLIED.

MOUNTING BOSSSES USE EITHER M2.5 METRIC
OR #4 STD. SHEET METAL SCREWS x 3/16 LG.
(NOT SUPPLIED)

NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED.

PART NO.	A	B	C	D	E	F	G	H	J
PC-11463	1.417	0.689	0.689	1.137	0.865	0.689	0.689	1.200	1.037
PC-11464	1.732	0.689	1.004	1.452	1.180	0.689	1.004	1.515	1.352
PC-11465	2.047	1.004	1.004	1.767	1.495	1.010	1.004	1.830	1.667

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PC-11463](#) [PC-11465](#) [PC-11464](#)