



April 2014

Common Mode Filters

With built-in ESD protection element type

TCE series

TCE0806G [0302 inch]*

TCE0806S [0302 inch]

TCE1608G [0603 inch]

* Dimensions Code JIS[EIA]

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

REMINDERS

- The storage period is less than 6 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 20 to 70% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Before soldering, be sure to preheat components.
The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications.
If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Carefully lay out the coil for the circuit board design of the non-magnetic shield type.
A malfunction may occur due to magnetic interference.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- Do not expose the products to magnets or magnetic fields.
- Do not use for a purpose outside of the contents regulated in the delivery specifications.
- The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.
The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

(1) Aerospace/Aviation equipment	(8) Public information-processing equipment
(2) Transportation equipment (cars, electric trains, ships, etc.)	(9) Military equipment
(3) Medical equipment	(10) Electric heating apparatus, burning equipment
(4) Power-generation control equipment	(11) Disaster prevention/crime prevention equipment
(5) Atomic energy-related equipment	(12) Safety equipment
(6) Seabed equipment	(13) Other applications that are not considered general-purpose applications
(7) Transportation control equipment	

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

Common Mode Filters

With built-in ESD protection element type

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders

Overview of the TCE Series

■ FEATURES

- EMC component with an ESD protective device (ESD suppressor) added to a conventional thin-film common mode filter based on the thin-film processing techniques and material technology cultivated from HDD head manufacturing.
- One component can be used both as a common mode noise countermeasure and for ESD protection.
- The number of parts and mounting area were greatly reduced.

■ APPLICATION

- Noise countermeasure and ESD protection for high-speed differential interfaces (USB2.0, MIPI, HDMI) for mobile devices and general consumer products such as smart phones, tablets, digital cameras, and portable music players.

■ PART NUMBER CONSTRUCTION

TCE	0806	G	900	2P	T	□□□
Series name	LxWxT Dimensions (mm)	Product internal code	Impedance (Ω) at 100MHz	Number of lines	Packaging style	Internal code
	0806 0.85x0.65x0.40	G	120 12	2P 2 lines	T Taping	
	1608 1.60x0.80x0.40	S	350 35	4P 4 lines		
			500 50			
			900 90			

■ OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

Type	Temperature range		Package quantity	Individual weight
	Operating temperature	Storage temperature*		
	(°C)	(°C)		
TCE0806G	-25 to +85	-25 to +85	10,000	1.1
TCE0806S	-25 to +85	-25 to +85	10,000	1.1
TCE1608G	-25 to +85	-25 to +85	4,000	2.4


* The Storage temperature range is for after the circuit board is mounted.

- RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. <http://www.tdk.co.jp/rohs/>
- Halogen-free: Indicates that Cl content is less than 900ppm, Br content is less than 900ppm, and that the total Cl and Br content is less than 1500ppm.

- All specifications are subject to change without notice.

Overview of the TCE Series

■ RECOMMENDED REFLOW PROFILE




Preheating			Soldering		Peak	
Temp.	Time		Temp.	Time	Temp.	Time
T1 150°C	T2 180°C	t1 60 to 120s	T3 230°C	t2 10 to 30s	T4 245°C	t3 5s max.

TCE series


TCE0806G Type




■ SHAPE & DIMENSIONS



■ RECOMMENDED LAND PATTERN



■ CIRCUIT DIAGRAM




TCE series **TCE0806G Type****■ ELECTRICAL CHARACTERISTICS****□ CHARACTERISTICS SPECIFICATION TABLE**

Common mode impedance [at 100MHz] [Ω]typ.	DC resistance (Ω)max. [1 line]	Cutoff frequency (GHz)typ.	Clamp voltage (V)max.	Rated current (A)max.	Rated voltage (V)max.	Insulation resistance (M Ω)min.	Part No.
90	$\pm 30\Omega$	3.5	5.0	100	0.1	10	1 TCE0806G-900-2P-T□□□

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Agilent Technologies
DC resistance	4338A	Agilent Technologies
Insulation resistance	4339A	Agilent Technologies


* Equivalent measurement equipment may be used.

TCE series **TCE0806G Type****■ ELECTRICAL CHARACTERISTICS****□ IMPEDANCE VS. FREQUENCY CHARACTERISTICS**

○ Measurement equipment

Product No.	Manufacturer
E4991A	Agilent Technologies

* Equivalent measurement equipment may be used.

□ INSERTION LOSS VS. FREQUENCY CHARACTERISTICS

○ Measurement equipment

Product No.	Manufacturer
E5071B	Agilent Technologies


* Equivalent measurement equipment may be used.

TCE series


TCE0806S Type




■ SHAPE & DIMENSIONS



■ RECOMMENDED LAND PATTERN



■ CIRCUIT DIAGRAM



TCE series TCE0806S Type

■ ELECTRICAL CHARACTERISTICS


□ CHARACTERISTICS SPECIFICATION TABLE

Common mode impedance [at 100MHz] (Ω)	DC resistance (Ω)max. [1 line]	Cutoff frequency (GHz)typ.	Clamp voltage (V)max.	Rated current (A)max.	Rated voltage (V)max.	Insulation resistance (M Ω)min.	Part No.
12	$\pm 7\Omega$	1.0	8.0	0.1	10	1	TCE0806S-120-2P-T□□□
35	$\pm 12\Omega$	1.8	7.0	0.1	10	1	TCE0806S-350-2P-T□□□
50	$\pm 15\Omega$	2.5	6.5	0.1	10	1	TCE0806S-500-2P-T□□□

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Agilent Technologies
DC resistance	4338A	Agilent Technologies
Insulation resistance	4339A	Agilent Technologies


* Equivalent measurement equipment may be used.

TCE series **TCE0806S Type****ELECTRICAL CHARACTERISTICS****IMPEDANCE VS. FREQUENCY CHARACTERISTICS**

○ Measurement equipment

Product No.	Manufacturer
E4991A	Agilent Technologies

* Equivalent measurement equipment may be used.

INSERTION LOSS VS. FREQUENCY CHARACTERISTICS

○ Measurement equipment

Product No.	Manufacturer
E5071B	Agilent Technologies


* Equivalent measurement equipment may be used.

TCE series

TCE1608G Type




■ SHAPE & DIMENSIONS




Dimensions in mm

■ RECOMMENDED LAND PATTERN



■ CIRCUIT DIAGRAM



• No polarity

TCE series TCE1608G Type

■ ELECTRICAL CHARACTERISTICS


□ CHARACTERISTICS SPECIFICATION TABLE

Common mode impedance (Ω) [at 100MHz] typ.	DC resistance (Ω)max. [1 line] min.	Cutoff frequency (GHz)typ.	Clamp voltage (V)max.	Rated current (A)max.	Rated voltage (V)max.	Insulation resistance (M Ω)min.	Part No.
90	60	1.95	5.0	100	0.1	10	1 TCE1608G-900-4P-T□□□

○ Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Agilent Technologies
DC resistance	4338A	Agilent Technologies
Insulation resistance	4339A	Agilent Technologies


* Equivalent measurement equipment may be used.

TCE series **TCE1608G Type****ELECTRICAL CHARACTERISTICS****IMPEDANCE VS. FREQUENCY CHARACTERISTICS**

○ Measurement equipment

Product No.	Manufacturer
E4991A	Agilent Technologies

* Equivalent measurement equipment may be used.

INSERTION LOSS VS. FREQUENCY CHARACTERISTICS

○ Measurement equipment


Product No.	Manufacturer
E5071B	Agilent Technologies

* Equivalent measurement equipment may be used.


TCE series

Packaging style

■ REEL DIMENSIONS



■ TAPE DIMENSIONS



Type	A	B	P1	K
TCE0806G	0.74	0.94	2.0	0.50
TCE0806S	0.74	0.94	2.0	0.50
TCE1608G	1.00	1.80	4.0	0.50

