

9154 Multi-Conductor - Single-Pair Cable

For more Information
please call

1-800-Belden1

**Description:**

20 AWG stranded (7x28) TC conductors, PVC insulation, twisted pair, overall Beldfoil® shield (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
1	20	7x28	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.3556

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
22	7x30		TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.7874

Overall Cabling

Overall Nominal Diameter: 5.029 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red

Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)
38.09985	26.248

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	29.615 Kg/Km
Max. Recommended Pulling Tension:	173.480 N
Min. Bend Radius (Install)/Minor Axis:	50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

C(UL) Flame Test:	FT4
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
36

Nom. Inductance:

Inductance (μH/m)
0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
196.86

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
328.1

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
31.1695

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
37.4034

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
4 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

METRIC MEASUREMENT VERSION

9154 Multi-Conductor - Single-Pair Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9154 290U1000	305 MT	9.979 KG	BEIGE, LIGHT		2 #20 PVC SHLD PVC
9154 290U500	152 MT	5.216 KG	BEIGE, LIGHT		2 #20 PVC SHLD PVC
9154 2901000	305 MT	10.433 KG	BEIGE, LIGHT	C	2 #20 PVC SHLD PVC
9154 290500	152 MT	5.443 KG	BEIGE, LIGHT	C	2 #20 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 10-03-2008

© 2011 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.