

1-1986714-0 Product Details

[!\[\]\(cf531ed27e91483460120fcc057b3901_img.jpg\) Share](#) [!\[\]\(34fde9b7c74442c0438f550a41236260_img.jpg\) Print](#) [!\[\]\(f3ffd03e145adb5d0f6f54d9f4fb82fd_img.jpg\) Email](#)

1-1986714-0

TE Internal Number: 1-1986714-0

 Active

Terminal Block Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)**Product Highlights:**

- Connector
- Type of Connector = Wire Receptacle
- Not Shrouded
- Housing Color = Green
- Side Stackable

[View all Features](#)**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- [POWER TERMINAL BLOCK, SOLDERABLE UP TO 275DEG C DOUB...](#) (PDF, English)

Additional Information:

- [Product Line Information](#)

Catalog Pages/Data Sheets:

- None Available

Related Products:

- [Tooling](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)**Product Features (Please use the Product Drawing for all design activity)****Product Type Features:**

- [Product Type](#) = Connector
- [Type of Connector](#) = Wire Receptacle
- [Shrouded](#) = No
- [Mount Angle](#) = Vertical
- UL File Number = E60677

Contact Features:

- [Threaded Flange](#) = Without
- [Screw Flange](#) = Without
- Contact Plating, Mating Area, Material = Tin over Steel

Electrical Characteristics:

- Current Rating, Max. (A) = 130
- Voltage (VAC) = 600

Housing Features:

- [Housing Color](#) = Green
- Housing Material = Polyamide

Body Features:

- [Side Stackable](#) = Yes
- [Number of Positions](#) = 10
- [Number of Rows](#) = Single
- [Centerline \(mm \[in\]\)](#) = 15.00 [0.591]
- [Wire Entry Diameter \(Solid Wire\) \(mm²\)](#) = 0.05 - 35.00
- [Wire Entry Diameter \(Stranded Wire\) \(mm²\)](#) = 0.05 - 25.00
- [Wire Entry Angle](#) = Side
- [Interlock](#) = Without
- Wire Range (mm [AWG]) = 0.50-41.00 [20-1]
- Pin Length (mm [in]) = 5.00 [0.197]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

Corporate Information[About TE](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)**Quick Links**[Check Distributor Inventory](#)[Cross Reference Products](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)**Customer Support**[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)**Keep Me Informed**

Receive TE News, Events & Technology Updates

Enter your email address

