









12X NO.20 WIRE LEAD PER MIL-W-22759/7 MARKED WITH
CIRCUIT IDENTIFICATION AND WIRE GAGE (1/20,2-20,ETC.)
PER MIL-W-5088 _____



TRAVEL CHARACTERISTICS




NOTES

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 4 - UNIT PROVIDES NO SHAFT RESTORING TORQUE, THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF THE SHAFT
 - 5 DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
 - 6 HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 7 SILVER PROJECTION, GOLD PLATED CONTACTS
 - 8 CIRCUITS ILLUSTRATED IN FREE POSITION ANGLE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (0) + 030

TWO PLACE (00) ± 015

THREE PLACE (000) $\pm$ 005

ANGLES $\pm$

ANGLES	H

WEIGHT 12.0 OZ MAX

CHARACTERISTICS
OPERATING FORCE - - - - - 3 IN LB MAX

ELECTRICAL DATA	
	CONTACT ARRANGEMENT 4X S P D T

LOAD	28 VDC	
	SEA LEVEL	50,000 FT
RES	7	7
IND	2.5	1.0

PRETRAVEL
DIFFERENTIAL TRAVEL
OVERTRAVEL
FREE POSITION

SEE DETAIL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[39EN222-6](#)