


FLKMS-D 9 SUB/B/ZFKKDS/PE

Order No.: 2295949

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2295949>

VARIOFACE module, with spring-cage connection and D-Subminiature socket strip, for mounting on NS 35/7,5 or NS 32, 9-pos.

Commercial data

GTIN (EAN)	4017918448028
sales group	I091
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0928 KG

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Number of positions	9
Status display	No
Ambient temperature (operation)	-20 °C ... 50 °C
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 664/IEC 664 A
	DIN VDE 0110
	DIN VDE 0109-11, draft

Pollution degree	2
Surge voltage category	II

Connection data

Connection 1	PCB connection
Connection in acc. with standard	IEC / EN
Type of connection	Spring-cage connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	7 mm
Connection 2	D-SUB connection
Type of connection	Pluggable
Number of positions	9

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;