





- 1 PART NO & DATE CODE MARKED (WHITE), .062±.015 HIGH CHARS. IN APPROX. AREA SHOWN WHEN HOUSING SIZE PERMITS.
- 2 CAVITY IDENT. MARKED (WHITE), .046±.015 HIGH CHARS., FIRST & EVERY FIFTH CAVITY, ONE SIDE AS SHOWN.
- 3 TOLERANCE NON-CUMULATIVE.
4. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 5 AMP LOGO MOLDED IN TEXTURED AREA AS SHOWN.
- 6 FLASH ALLOWED TO BE .015 IN THIS AREA.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG CHK S. SHUEY APVD D. DUPLER	21-JUN-95 21-JUN-95 21-JUN-95	 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME									
		0 PLC ± -		HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN -									
		1 PLC ± -											
		2 PLC ± 0.13[.005]											
		3 PLC ± -											
		4 PLC ± -											
ANGLES ± -		PRODUCT SPEC		SIZE A2									
MATERIAL		APPLICATION SPEC						CAGE CODE 00779		DRAWING NO C=87499		RESTRICTED TO	
FINISH		WEIGHT -						SHEET		REV			
FLAME RETARDANT		-		CUSTOMER DRAWING				SCALE 4:1		SHEET 2 of 2		REV U3	