



LEAD FINISH:	SILVER
BUSHING FINISH:	SILVER
CAPACITANCE	10pF ±20%
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C -- VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	

FREQ. MHz	I.L. (db)
1	N/A
100	N/A
500	N/A
1 GHz	N/A
10 GHz	N/A

SCHEMATIC

MARKING:
PART: SF100M
BAG:
SCI 54F-779-073 DATE CODE QTY/BAG (200 MAX.)

	00	REV. N	TOLERANCES UNLESS OTHERWISE SPECIFIED		FAIRVIEW PENNSYLVANIA
	00	CHANGE NOTICE	Fractions ± 1/64	SPECTRUM CONTROL INC.	
			Dec. .xx±	Dwn. KAUFFMAN	Description FEED THRU
			Dec. .xxx±.005	Date 2-28-08	RESIN SEAL FILTER
			Angles ±0° 30'	Engr. J.KRAUS	
			CODE IDENT. NO. OLSP2	Scale NONE	54F-779-073
CN 40123-ENG					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[54F-779-073](#)