






PRODUCT NO.
SEE TABLE




mat'l. code				surface ISO 1302	☒	tolerance ISO 406 ISO 1101	projection 	product family CLINCHER	
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM scale 4:1	title CLINCHER™ LATCH HEADER VERTICAL SELF-RETAINING
C	V60842	EPK	6/3/96	angles	linear	.XX±.01/.X±0.3			
D	V71289	HTB	9/22/97			.XXX±.006/.XX±0.13			
E	M05-0109	MHT	7/15/05	0°±2°	.XXX±.0020/.XXX±0.05				
F	M06-0052	MHT	1/30/06	dr	T.BREWBAKER	5/23/95			
G	M06-0233	AGS	6/13/06	engr	T.HANNA	2/17/05			
H	M08-0304	MHT	10/16/08	chr	T.HANNA	2/17/05		dwg no 95735 sheet 1 of 2 size A3	
J	M09-0079	MHT	5/22/09	appd	T.HANNA	2/17/05			
sheet index	revision sheet	J	J						
		1	2						

PRODUCT NUMBER	NO. OF POSITIONS	DIM K ENGLISH	DIM K METRIC	DIM L ENGLISH	DIM L METRIC	RETENTION LEG
NOTE 8						
95735-X02	1 X 2	0.400	10.16	0.100	2.54	NOTE 5
95735-X03	1 X 3	0.500	12.70	0.200	5.08	NOTE 6
95735-X04	1 X 4	0.600	15.24	0.300	7.62	NOTE 7
95735-X05	1 X 5	0.700	17.78	0.400	10.16	
95735-X06	1 X 6	0.800	20.32	0.500	12.70	
95735-X07	1 X 7	0.900	22.86	0.600	15.24	
95735-X08	1 X 8	1.000	25.40	0.700	17.78	
95735-X09	1 X 9	1.100	27.94	0.800	20.32	
95735-X10	1 X 10	1.200	30.48	0.900	22.86	
95735-X11	1 X 11	1.300	33.02	1.000	25.40	
95735-X12	1 X 12	1.400	35.56	1.100	27.94	
95735-X13	1 X 13	1.500	38.10	1.200	30.48	
95735-X14	1 X 14	1.600	40.64	1.300	33.02	
95735-X15	1 X 15	1.700	43.18	1.400	35.56	
95735-X16	1 X 16	1.800	45.72	1.500	38.10	NOTE 7

DASH NO	OVERPLATING	UNDERPLATING
-1YY	30u"/.76u MIN Au OR GXT	50u"/1.27u MIN Ni
-1YYLF		
-4YY	100u"/2.54u MIN PURE TIN	
-4YYLF		

95735-X YY LF
 LEAD FREE OPTION (NOTE 8)
 NO. OF POSITIONS
 PIN PLATING (SEE TABLE)
 BASE PART NUMBER



SCALE 3/1
RECOMMENDED HOLE PATTERN

NOTES:

- MOLDING MATERIAL: HIGH TEMPERATURE PLASTIC FLAME RETARDENT PER UL-94V-0. COLOR: NATURAL
- PIN MATERIAL: 3/4 HD PHOS. BRONZE
- LOGO TO BE LOCATED APPROX. AS SHOWN.
- TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.
- RETENTION LEGS POS. 1 & 2 RETENTION FEATURE ROTATED 90° FROM THAT SHOWN.
- RETENTION LEGS POS. 1 & 3 RETENTION FEATURE ROTATED 90° FROM THAT SHOWN.
- RETENTION LEGS CENTER 4 POS. ONLY AS SHOWN.
- FOR LEAD FREE OPTION ADD "LF" IN THE END OF THE EXISTING PART NUMBERS.
- IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE
- PLATING OPTIONS: MAYBE EITHER GOLD OR GXT PLATED AT MANUFACTURER CHOICE

mat'l. code	surface	tolerance	projection	product family
ISO 1902	ISO 406	ISO 1101	ISO 1101	CLINCHER
tr	ecn no	dr	date	title
J				CLINCHER™ LATCH HEADER
				VERTICAL SELF-RETAINING
				dwg no
				95735
				sheet 2 of 2
				size A3
				type
				Product Customer Drawing
sheet	revision			
index	sheet			