

Dual Field Programmable Blank Oscillator

Series **CPPD**

- Programmed on the fly with the PG-3000 field oscillator programming instrument within seconds
- Full Programming available for each frequency
- Provides a sealed finished custom oscillator
- Standard Package Options
- The dual FIPO contains a frequency select function. For example, consumer products often require different electrical standards around the world. Ex: Converting PAL to NTSC by changing FS line or modem real-time switching between transmit and receive frequencies



Part Numbering Example: CPPD C 1 L Z - A5 B6 - XX.XXXX / YY.YYYY

CPPD	C	1	L	Z	A5	B6	XX.XXXX	YY.YYYY
SERIES	OUTPUT	PACKAGE STYLE	VOLTAGE	ADDED FEATURES	OPERATING TEMP.	STABILITY	FREQ. F0	FREQ. F1
CPPD	C = CMOS T = TTL	1 = Full Size 4 = Half Size 5 = 3.2X5 Ceramic 7 = 5X7 Ceramic 8 = PLASTIC SMD	Blank = 5V L = 3.3 V R = 2.7 V	Blank = Bulk T = Tube Z = Tape and Reel	Blank = 0°C +70°C A5 = -20°C +70°C A7 = -40°C +85°C	B6 = ±100 ppm BP = ±50 ppm BR = ±25 ppm	1.000~133.000 MHz PIN 1 Logic "0"	1.000~133.000 MHz PIN 1 Logic "1"

Specifications:

Description	Min	Typ	Max	Unit
Frequency Range: Programmable to Any Discrete Frequency	1.000		133.000	MHz
Available Stability Options:	-100 -50 -25		100 50 25	ppm ppm ppm
Programmable Input Voltage: (1–133 MHz) (1–100 MHz) (1–66 MHz)	4.5 3.0 2.5	5.0 3.3 2.7	5.5 3.6 3.0	V V V
Operating Temperature Range Options:	0 -20 -40		+70 +70 +85	°C °C °C
Storage Temperature:	-55		+125	°C
Aging (PPM/1st Year) Ta=25°C, Vdd=5/3.3V PPM/Year (after 1st year)			±5 ±1	
Programmable Output Level: TTL/CMOS				
Packaging: Tape and Reel (1K per Reel) Tube Bulk				

Operating Conditions:

Description	Min	Max	Unit
Vdd Supply Voltage	3.0	5.5	V
CTTL Max Capacitive Load on outputs for TTL levels 4.5V–5.5V Vdd ≤ 40 MHz 4.5V–5.5V Vdd > 40–133 MHz		50 25	pF pF
CCMOS Max Capacitive Load on outputs for CMOS levels 4.5V–5.5V Vdd, ≤ 66 MHz 4.5V–5.5V Vdd, 66–133 MHz 3.0V–3.6V Vdd, ≤ 40 MHz 3.0V–3.6V Vdd, 40–100 MHz 2.5V–3.0V Vdd, ≤ 66 MHz		50 25 30 15 25	pF pF pF pF pF



Dual Field Programmable Blank Oscillator**Series CPPD**

- *Programmed on the fly with the PG-3000 field oscillator programming instrument within seconds*
- *Full Programming available for each frequency*
- *Provides a sealed finished custom oscillator*

Electrical Characteristics

Description	TEST CONDITIONS	Min	Typ	Max	Unit
Input Characteristics (Pin 1):					
CONTROL PIN	4.5–5.5V Vdd			0.8	V
V _{IL} , Low-Level Input Voltage	3.0–3.6V Vdd			0.2Vdd	V
TO SWITCH TO F0 OUTPUT	2.5–3.0V Vdd			0.2Vdd	V
V _{IH} , High-Level Input Voltage	4.5–5.5V Vdd	2.0			V
TO SWITCH TO F1 OUTPUT	3.0–3.6V Vdd	0.7Vdd			V
	2.5–3.0V Vdd	0.7Vdd			V
I _{IL} , Input Low Current	V _{IN} = 0V			10	μA
I _{IH} , Input High Current	V _{IN} = Vdd			5	μA
Output Characteristics:					
V _{OL} , Low-Level Output Voltage	4.5V–5.5V Vdd, 16 mA I _{OL}			0.40	V
	3.0V–3.6V Vdd, 8 mA I _{OL}			0.4	V
V _{OHTTL} , High-level Output Voltage TTL	4.5V–5.5V Vdd, -16 mA I _{OL}	2.4			V
V _{OHCMOS} , High-level CMOS Voltage	4.5V–5.5V Vdd, -16 mA I _{OL}	Vdd-0.4			V
	3.0V–3.6V Vdd, -8 mA I _{OL}	Vdd-0.4			V
	2.5–3.0V VDD, 6mA	Vdd-0.4			V
Power Supply Current: (unloaded)	4.5–5.5 Vdd, OUTPUT FREQ ≤ 133 MHz			45	mA
	3.0–3.6 Vdd, OUTPUT FREQ ≤ 100 MHz			25	mA
	2.5–3.0 Vdd, Output Freq ≤ 66 MHz			20	mA
Input Pull-Up Resistor (Pin 1)	4.5–5.5 Vdd, V _{IN} = 0V	1.1	3.0	8.0	MΩ
	4.5–5.5 Vdd, V _{IN} = 0.7V	50	100	200	KΩ
Frequency Select Switching Time				500	μs



Dual Field Programmable Blank Oscillator**Series CPPD**

- *Programmed on the fly with the PG-3000 field oscillator programming instrument within seconds*
- *Full Programming available for each frequency*
- *Provides a sealed finished custom oscillator*

Output Clock Switching Characteristics

Description	TEST CONDITIONS	Min	Typ	Max	Unit
Duty Cycle: TTL @ 1.4 V 4.5-5.5 Vdd	≤ 50 MHz, C _L = 50 pF	45		55	%
	50-66 MHz, C _L = 15 pF	45		55	%
	66-125 MHz, C _L = 25 pF	40		60	%
	125-133 MHz, C _L = 15 pF	40		60	%
Duty Cycle: CMOS @ Vdd/2 4.5-5.5 Vdd 3.0-3.6 Vdd	≤ 66 MHz, C _L ≤ 25 pF	45		55	%
	66-125 MHz, C _L ≤ 25 pF	40		60	%
	125-133 MHz, C _L ≤ 15 pF	40		60	%
	≤ 40 MHz, C _L ≤ 30 pF	45		55	%
	40-100 MHz, C _L ≤ 15 pF	40		60	%
Output Clock Rise/Fall	0.8V-2.0V, 4.5-5.5 Vdd, C _L = 50			1.8	ns
	0.8V-2.0V, 4.5-5.5 Vdd, C _L = 25			1.2	ns
	0.8V-2.0V, 4.5-5.5 Vdd, C _L = 15			0.9	ns
	0.2-0.8Vdd, 4.5-5.5 Vdd, C _L = 50			3.4	ns
	0.2-0.8Vdd, 3.0-3.6 Vdd, C _L = 30			4.0	ns
	0.2-0.8Vdd, 3.0-3.6 Vdd, C _L = 15			2.4	ns
Start Up Time	From power on			10	ms
RMS Period Jitter:	1 – 133 MHz		8	11	ps
Peak to Peak *	≤ 33.000 MHz		65	99	ps
	> 33.000 MHz		65	80	ps

* Jitter tested at > 1,000,000 samples, exceeding JEDEC std JESD65.






Field Programmable Blank Oscillator

Note: *Bypass Vdd to GND with a 0.01 μ F capacitor*

Style 1 Full Size 14 Pin Dip




STYLE 1 FULL SIZE 14 PIN DIP



PIN FUNCTION
1 CONTROL
7 GND
8 OUTPUT
14 Vdd




Style 4 Half Size 8 Pin Dip

STYLE 4 HALFSIZE 8 PIN DIP





PIN FUNCTION
1 CONTROL
4 GND
5 OUTPUT
8 Vdd

Style 7 5x7 Ceramic SMD



PIN FUNCTION
1 CONTROL
2 GND
3 OUTPUT
4 Vdd

Style 8 Plastic SMD



PINOUT
1 OE
2 GND
3 OUTPUT
4 Vdd

Field Programmable Blank Oscillator

Note: *Bypass Vdd to GND with a 0.01 μ F capacitor*

Style 5 3.2x5 Ceramic SMD

