




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.


MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

- TUSONIX STANDARD PART
NUMBER: 4100-002.
TUSONIX RoHS COMPLIANT PART
NUMBER: 4100-002 LF.
CUSTOMER MUST SPECIFY STANDARD OR
RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED.
RoHS PART #: SILVER PLATED.
- EYELET FINISH: STANDARD PART #: 60/40 SOLDER PLATED.
RoHS PART #: SILVER PLATED.
- PART MARKING: STANDARD, NO MARKING.
RoHS PART: GREEN DOT ON INSULATION BAND,
TYPICAL LOCATION.

MIN. CAP. pF	WORKING VOLTAGE		CURRENT Idc.	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
1500	350	200	15 A	10 G	700	5	25	60	60

X-2015 Rev-0	REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified		Title EYELET STYLE EMI FILTER	
	Original Release C.O. 1653		0		DECIMAL ± .031 [0.79]		Drawn S.M. 07-13-00 Scale 6 X	
	CURRENT UNIT "A" ADDED L.E. 08-20-85				ANGLES ± 		Approved T.C. 07-13-00	
	2595		1		TUSONIX TUCSON, ARIZONA		A 4100-002	
	RND TO COMP FMT. S.M. 07-18-00							
	20000717-5-06		2					
ADDED NOTES, IR, DWV & CIRCUIT. S.M. 06-06-05				20050526-4-06		3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4100-002LF](#)