
**Feature -**


Multiple keys and poles  
interlock and individual lock

**Application -**




various switching purpose  
in all home electronic equipments  
and industrial electronic equipments


**► SPECIFICATIONS**




SWITCH SPECIFICATIONS	
POLE - POSITION	2P2T , 4P2T , 6P2T , Momentary and Lock Type are Available
CONTACT RATING	30 V DC , 0.1 A
CONTACT RESISTANCE	40 mΩ MAX. 1.5 V DC ; 100 mA , by Method of Voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 500 V AC for 1 Minute
OPERATING FORCE	250 ± 150gf
OPERATING LIFE	10,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	TRAVEL : 1.5 ± 0.3 mm TOTAL TRAVEL : 3.0 ± 0.3 mm

**► HOW TO ORDER**





### ► DIMENSION

**PD - S2L**

**PD - S4L**

**PD - S6L**


### ► P.C.B LAYOUT

**PD - S2L**

**PD - S4L**

**PD - S6L**


### ► SCHEMATIC

**2 POLE**

**4 POLE**

**6 POLE**


### ► MATERIAL

- COVER : PA + GF
- ACTUATOR : PA + GF
- BASE FRAME : PA + GF
- TERMINAL : SILVER PLATING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Well Buying:

[PD-S4L](#) [PD-S2L-2](#) [PD-S2L](#)