





LOC	DIST	REVISIONS				
CM	0	P	LTR	DESCRIPTION	DATE	DWN
						APVD
		D		REVISED PER 0G3B-0237-05	9/21/05	SS



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.12 – 0.4MM² (26–22 AWG).
3. INSULATION RANGE: 1.19–1.75[.047–.069] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

$\triangle 5$	0.25[.010] BRASS	1-794226-0
$\triangle 1$	0.25[.010] BRASS	794226-3
PRE-TIN	0.25[.010] BRASS	794226-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME		
	0 PLC ± -		PRODUCT SPEC	PIN, LOOSE PIECE, MINI UNIVERSAL MATE-N-LOK 2		
	1 PLC ± -		APPLICATION SPEC			
MATERIAL	2 PLC ± -		WEIGHT	SIZE	CAGE CODE	DRAWING NO
	3 PLC ± 0.15 [.006]		-	A2	00779	C=794226
SEE TABLE	4 PLC ± -		CUSTOMER DRAWING			RESTRICTED TO
	ANGLES ± -		SCALE 10:1			-
SEE TABLE		FINISH	SHEET 1 of 1			REV D