








LOC		DIST		REVISIONS					
CM	53	P	LTR	DESCRIPTION			DATE	OWN	APVD
		G		REV & REDWN PER EC 061B-0087-99			04-JUN-99	KW	J5

1. RECOMMENDED PANEL THICKNESS 2.29 MAX.
2. OPTIONAL CONSTRUCTION.
3. MARKING FOR UL LOGO AND CSA LOGO LOCATED APPROXIMATELY AS SHOWN.



3-DIMENSIONAL MODEL
NTS

16.13	.635	-	-
5.03	.198	41.28	1.625
2.36	.093	31.50	1.240
2.29	.090	27.18	1.070
0.38	.015	27.05	1.065
0.25	.010	25.40	1.000
0.13	.005	16.64	.655
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	04-JUN-1999	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK J. SCHLUNZ	04-JUN-1999		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. SCHLUNZ	04-JUN-1999	NAME	
mm		PRODUCT SPEC		RECEPTACLE, 15 CIRCUIT, .093 COMMERCIAL PIN AND SOCKET	
0 PLC ±-		APPLICATION SPEC		SIZE	
1 PLC ±-		WEIGHT		CAGE CODE	
2 PLC ±0.13		CUSTOMER DRAWING		DRAWING NO	
3 PLC ±-		SCALE		RESTRICTED TO	
4 PLC ±-		SHEET		REV	
ANGLES		4:1		1 OF 1	
FINISH		770103		REV	
MATERIAL NYLON, JL 94V-2, NATURAL		770103		G	