


Tin Coated Split Point Jobber Drills



DIN 338/BS 328

Flute geometry

Right hand spiral and wider flutes

Point angle

118° special Dormer "P.S. Point" giving higher positional accuracy

Surface treatment

Tin coated (Titanium Nitride coating)

Application

High speed steel tin coated jobber drill allows increased cutting speed and improved tool life.

493986

Metric

Size (mm)	Flute Length (mm)	Overall Length (mm)	Order Code	Price Each
3.00	33	61	138-9516	
3.20	36	65	138-9528	
3.30	36	65	138-9529	
3.40	39	70	138-9530	
3.50	39	70	138-9517	
3.70	39	70	138-9532	
3.80	43	75	138-9533	
4.00	43	75	137-4251	
4.10	43	75	138-9534	
4.20	43	75	138-9535	
4.30	47	80	138-9536	
4.50	47	80	148-5506	
4.90	52	86	137-4257	
5.00	52	86	138-9519	
5.10	52	86	138-9538	
5.20	52	86	138-9539	
5.50	57	93	137-4252	
5.70	57	93	138-9540	
6.00	57	93	137-4253	
6.50	63	101	138-9521	
6.80	69	109	138-9522	
7.00	69	109	138-9523	
7.20	69	109	138-9541	
7.50	69	109	148-5508	
7.70	75	117	138-9542	
8.00	75	117	138-9524	
8.20	75	117	138-9544	
8.50	75	117	138-9525	
8.70	81	125	138-9545	
9.00	81	125	138-9526	
9.50	81	125	148-5509	
10.00	87	133	148-5510	
10.20	87	133	148-5511	
10.50	87	133	137-4255	
11.00	94	142	148-5512	
11.50	94	142	148-5513	
12.00	101	151	138-9527	
12.50	101	151	148-5514	

Fractional

Size	Flute Length	Overall Length	Order Code	Price Each
½"	36mm	65mm	137-4256	